

Drg No :- C 44608

INSTALLATION DRAWING

SPECIFICATION

ACTUATING FORCE:- 5.0N(18ozf)MAX

RELEASE FORCE :- 1.7N(6.0ozf)MIN

FREE POSITION :- 42.0 (1.65) MAX

OPERATING POSITION:- 39.7 ± 1.5 (1.56)



MOVEMENT DIFFERENTIAL :- 0.4 (0.016)MAX

OVERTRAVEL (AVAILABLE) :- 4.75(0.19)

SPECIAL FEATURE :-
TESTED AND STAMPED TO UL AND
CSA REQUIREMENTS

APPROVAL RATING :-
15AMP - 250 V.A.C.
1/3HP - 125 OR 250 V.A.C.

DIAGRAM OF CONNECTIONS



UNCONTROLLED ISSUE
THIS ISSUE WILL NOT BE KEPT UP TO DATE

23 JAN 2003		
1	FIRST ISSUE	18/09/02
ISSUE	REVISION	DATE

saia-burgess

Smart solutions for comfort and safety

Saia-Burgess Gateshead Limited
Dukesway, Team Valley Trading Estate
Gateshead, Tyne & Wear NE11 0UB
Tel: +44(0) 191 401 6100
Fax: +44(0) 191 401 6322
www.saia-burgess.co.uk



DO NOT SCALE!

THIS DRAWING MUST ONLY BE
AMENDED ON A CAD SYSTEM

ALL DIMENSIONS SPECIFIED
IN MILLIMETRES

TOLERANCES UNLESS STATED:

3 DECIMAL PLACES ± 0.01
2 DECIMAL PLACES ± 0.05
2 DECIMAL PLACES ± 0.15
ANGULAR $\pm 1^\circ$
INCH - OUNCE UNITS [IN BRACKETS]

DRAWN

DATE

SCALE

T.BELL

18/09/02

2/1

APPROVED

CHECKED BY

ENGINEERING

QUALITY ASSURANCE

TITLE / DESCRIPTION

VCF9QR1 - UL

Drg No :- C 44608

A3