



Main

Range	EasyPact
Product name	EasyPact TVR
Product or component type	Contactor
Device short name	LC1R
Contactor application	Resistive load Motor control Reversing
Utilisation category	AC-3 AC-1
Poles description	3P
Power pole contact composition	3 NO
[Ie] rated operational current	25 A (at <40 °C) at <= 400 V AC AC-3 for power circuit 32 A (at <40 °C) at <= 400 V AC AC-1 for power circuit
[Uc] control circuit voltage	110 V AC 50 Hz
Auxiliary contact composition	1 NO
[Ue] rated operational voltage	Power circuit: 690 V AC 50 Hz Signalling circuit: 690 V AC 50 Hz

Complementary

Motor power kW	5.5 KW at 220/230 V AC 50 Hz 11 KW at 380/400 V AC 50 Hz 15 kW at 660/690 V AC 50 Hz
Electrical durability	1 Mcycles 25 A AC-3 at Ue <= 440 V
Mechanical durability	10 Mcycles
Maximum operating rate	1200 cyc/h 40 °C
Operating time	12...22 ms closing 4...19 ms opening
Control circuit voltage limits	Operational: 0.85...1.1 Uc Drop-out: 0.2...0.75 Uc
Hold-in power consumption in VA	8.3 VA cos phi 0.3
[Ith] conventional free air thermal current	32 A (at 40 °C) for power circuit 10 A (at 40 °C) for signalling circuit
Average impedance	2.5 mOhm - Ith 32 A 50 Hz for power circuit
Power dissipation per pole	AC-3: 1.25 W AC-1: 3.2 W
Heat dissipation	2...3 W at 50 Hz
Irms rated making capacity	250 A 380 V AC power circuit AC-3 IEC 60947 250 A 380 V AC power circuit AC-3 GB 14048
Rated breaking capacity	200 A at 380 V for power circuit AC-3 conforming to IEC 60947 200 A at 380 V for power circuit AC-3 conforming to GB 14048
[Icw] rated short-time withstand current	100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit 145 A 40 °C - 10 s for power circuit 84 A 40 °C - 1 min for power circuit 40 A 40 °C - 10 min for power circuit

Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 32 A gG at <= 690 V coordination type 1 for power circuit
Overvoltage category	III
[Ui] rated insulation voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-1 Power circuit: 690 V conforming to GB 14048.4
Coil technology	Without built-in suppressor module
Auxiliary contacts type	Type mechanically linked 1 NO conforming to IEC 60947-5-1
Signalling circuit frequency	50 Hz
Minimum switching current	5 mA for signalling circuit
Switching voltage	17 V for signalling circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MΩ for signalling circuit
Mounting support	Plate Rail
Connections - terminals	Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 1...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 1...4 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 1.5...6 mm <sup>2</sup> - external diameter: 10 mm - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...2.5 mm <sup>2</sup> - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...2.5 mm <sup>2</sup> - cable stiffness: solid without cable end
Tightening torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 M4 Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 M4
Height	74 mm
Width	45 mm
Depth	85 mm
Standards	IEC 60947-1 GB 14048.4 IEC 60947-4-1 GB 14048.1
Product certifications	CCC

## Environment

Pollution degree	3
Protective treatment	TH conforming to IEC 60068-2-30
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-40...60 °C
Permissible ambient air temperature around the device	-20...55 °C at Uc
Operating altitude	2000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-11
Mechanical robustness	Vibrations contactor open (1.2 gn, 5...300 Hz) conforming to IEC 60068-2-6 Vibrations contactor closed (2.5 Gn, 5...300 Hz) conforming to IEC 60068-2-6 Shocks 11 ms contactor closed (8 gn) conforming to IEC 60068-2-27 Shocks 11 ms contactor open (4 gn) conforming to IEC 60068-2-27

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8.5 cm
Package 1 Length	7.4 cm
Package 1 Weight	345 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins