


## Cable marker - US-WMTB (29X8) VT - 0829330

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, Card, violet, unlabeled, can be labeled with: THERMOMARK CARD, Mounting type: Thread on, Cable diameter: >13 mm, Lettering field: 29 x 8 mm




The figure shows the US-WMTB (24x5) version

### Why buy this product

- The US-WMTB... UniSheet labeling range includes markers that can be secured using standard cable binders
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated marking strips are easy to separate and can be easily fitted
- The sheets provide space for including function texts



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 613354
Weight per Piece (excluding packing)	13.65 g
Custom tariff number	39204910
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	29 mm
Width (a)	16 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing.

#### General

Color	violet
-------	--------

# Cable marker - US-WMTB (29X8) VT - 0829330

## Technical data

### General

Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	24
Number of individual labels per row	6
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
Ink ribbon	5146451 THERMOMARK CARD-US-MAG1
	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	Thread on

## Classifications

### eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761

## Cable marker - US-WMTB (29X8) VT - 0829330

### Classifications

#### ETIM

ETIM 4.0	EC001530
ETIM 5.0	EC001530

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

### Accessories

#### Accessories

#### Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards