

## Cable marker - MM-WML 7,5 (24X13)R C1 WH/BK - 1116198

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marker, Roll, white/black, can be labeled with: THERMOMARK GO: without print, mounting type: adhesive, lettering field size: 22 x 12.7 mm, Number of individual labels: 165

### Product Description

MM-WML... vinyl polymer self-adhesive labels are available as prepunched material for wire marking.

### Your advantages

- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- ✓ The pre-punched geometry enables easy and convenient use
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- ✓ No visible difference between retrospective marking and existing markings created with a desktop roll printer
- ✓ The transparent protective foil is wound over the marking and provides permanent protection against contamination and abrasion
- ✓ The wrap-around labels do not add bulk, which means that the cable can still be drawn through cable ducts, for example
- ✓ The material is cUL certified
- ✓ Thanks to the innovative material composition, each label can be printed which results in zero wastage



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 042301
GTIN	4063151042301
Weight per Piece (excluding packing)	71.000 g
Country of origin	China
Sales Key	BG221E

### Technical data

#### Dimensions

Length (b)	24 mm
Width (a)	36.5 mm
Cable diameter	≤ 7.5 mm

# Cable marker - MM-WML 7,5 (24X13)R C1 WH/BK - 1116198

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended storage conditions	21 °C / 50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

### General

Color	white/black
Components	Free from silicone and cadmium
Material	Vinyl polymer
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Number of individual labels	165
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

### ETIM

ETIM 7.0	EC001530
----------	----------

## Cable marker - MM-WML 7,5 (24X13)R C1 WH/BK - 1116198

### Approvals

#### Approvals

---

#### Approvals

cULus Recognized

---

#### Ex Approvals

---

### Approval details

cULus Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>

MH48542