

# Product datasheet

Specifications



## Rack PDU, Basic, 1U, 22kW, 400V, (6) C19



AP7526

 **Discontinued on:** 01-Nov-2020

 **Discontinued**

### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Main

|                           |                    |
|---------------------------|--------------------|
| Colour                    | Black              |
| Product or component type | PDU                |
| PDU type                  | Basic              |
| Cord length               | 2.4 m              |
| Number of cables          | 1                  |
| Provided equipment        | Installation guide |

### Complementary

|                          |                            |
|--------------------------|----------------------------|
| Input Voltage            | 400 V 3 phases             |
| Height                   | 4.4 cm                     |
| Width                    | 43.7 cm                    |
| Output Voltage           | 230 V                      |
| Depth                    | 25.4 cm                    |
| Net weight               | 4.84 kg                    |
| Mounting location        | Front<br>Rear              |
| Mounting preference      | No preference              |
| Input Plug Type          | IEC 60309 32 A 3P + N + PE |
| Mounting mode            | Rack-mounted               |
| Rack units               | 1U                         |
| Mounting position        | Horizontal                 |
| Permissible voltage      | 200...250 V                |
| Max line current         | 32 A                       |
| Input current limits     | 32 A                       |
| Load capacity            | 22000 VA                   |
| Network frequency        | 47...63 Hz                 |
| Outlet type and quantity | 6 IEC 60320 C19            |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

|                                       |                                   |
|---------------------------------------|-----------------------------------|
| Product certifications                | CE<br>GOST<br>VDE                 |
| Ambient air temperature for operation | -5...45 °C                        |
| Relative humidity                     | 5...95 %                          |
| Operating altitude                    | 0...10000 ft                      |
| Ambient air temperature for storage   | -25...65 °C                       |
| Storage Relative Humidity             | 5...95 %                          |
| Storage altitude                      | 0.0000000000...15240.0000000000 m |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 24.1 cm  |
| Package 1 Width              | 55.9 cm  |
| Package 1 Length             | 50.2 cm  |
| Package 1 Weight             | 6.965 kg |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

|  Environmental footprint |                                               |
|-----------------------------------------------------------------------------------------------------------|-----------------------------------------------|
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)                                                     | 124                                           |
| Environmental Disclosure                                                                                  | <a href="#">Product Environmental Profile</a> |

Use Better

|  Materials and Substances |                                           |
|------------------------------------------------------------------------------------------------------------|-------------------------------------------|
| Packaging made with recycled cardboard                                                                     | Yes                                       |
| Packaging without single use plastic                                                                       | No                                        |
| <a href="#">EU RoHS Directive</a>                                                                          | Compliant                                 |
| REACH Regulation                                                                                           | <a href="#">REACH Declaration</a>         |
| Halogen content performance                                                                                | Product contains halogen above thresholds |

|  Energy efficiency |                          |
|-------------------------------------------------------------------------------------------------------|--------------------------|
| Optimized Energy Efficiency                                                                           | Energy efficient product |

Use Again

|  Repack and remanufacture |                                         |
|--------------------------------------------------------------------------------------------------------------|-----------------------------------------|
| Circularity Profile                                                                                          | <a href="#">End of Life Information</a> |
| Take-back                                                                                                    | Yes                                     |