






7908A5

Standard Series High Precision Angular Contact Ball Bearings



Boundary Dimensions

d	40	mm	Bore diameter
D	62	mm	Outside diameter
B	12	mm	Width
r(min.)	0.6	mm	Chamfer Dimension
r1(min.)	0.3	mm	Chamfer Dimension

Basic Load Ratings

Cr	18.1	kN	Basic Dynamic Load Rating
C0r	11.2	kN	Basic Static Load Rating

Speeds

Grease	19700	min-1	Limiting Speed
Oil (Oil-air)	29500	min-1	Limiting Speed

Dimensions

	A5: 25°		Contact Angle
a	17.9	mm	Effective Load Center

Abutment and Fillet Dimensions

da(min.)	45	mm	Diameter of Shaft Abutment
Da(max.)	57	mm	Diameter of Housing Abutment
Db(max.)	59.5	mm	Diameter of Housing Abutment
ra(max.)	0.6	mm	Radius of Shaft or Housing Fillet
rb(max.)	0.3	mm	Radius of Shaft or Housing Fillet

Performance

Pa	8.90	kN	Permissible Axial Load
----	------	----	------------------------

Preload,Rigidity(DB and DF arrangement)

	Preload	Axial Rigidity	Measured axial clearance
EL	68N	81N/μm	-1μm
L	113N	97N/μm	-3μm
M	291N	139N/μm	-9μm
H	572N	182N/μm	-16μm

Additional information

	0.70	g/brg	Recommended Grease Quantities
--	------	-------	-------------------------------

Mass

	0.110	kg	Mass(approx.)
--	-------	----	---------------



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 10:22 (UTC)



Table A		EL	L	M	H
	15°	6.5	6.0	5.0	4.5
	25°	2			
	30°	1.4			

Table B	DBD	DBB
Preload factor	1.36	2
Axial rigidity	1.48	2
Radial rigidity	1.54	2

Calculation of radial rigidity

Multiply axial rigidity by the appropriate factor in Table A.

Calculation of preload and axial rigidity for combined bearings

Multiply by the appropriate factor in Table B. For radial rigidity, multiply the value from Table A with the appropriate factor in Table B.