KEMET Part Number: C0603C159C1GACTU

(C0603C159C1GAC7867)



SMD Comm C0G, Ceramic, 1.5 pF, +/-0.25 pF, 100 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0603



Dimensions	
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
Т	0.8mm +/-0.07mm
S	0.7mm MIN
В	0.35mm +/-0.15mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

General Information		
Supplier:	KEMET	
Series:	SMD Comm C0G	
Style:	SMD Chip	
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I	
Features:	Ultra-Stable, Low Loss, Class I	
RoHS:	Yes	
Termination:	Tin	
Marking:	No	
Chip Size:	0603	

Specifications		
Capacitance:	1.5 pF	
Capacitance Tolerance:	+/-0.25 pF	
Voltage DC:	100 VDC	
Dielectric Withstanding Voltage:	250 VDC	
Temperature Range:	-55/+125C	
Temperature Coefficient:	COG	
Dissipation Factor:	0.10% 1MHz 25C	
Aging Rate:	0% Loss/Decade Hour	
Insulation Resistance:	100 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

