



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Receptacle**

Post Diameter: **.76 mm [.03 in ]**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **15**

Features

Product Type Features

Product Type	Connector
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
D-Sub Shell Size	2
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Blindmate	No

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	15
Power/Signal/Coax Combination	No

Body Features

Box Mount D-Sub Connector Insert Arrangement	MS18274-1
Shell Material	Steel
Shell Plating Material	Cadmium
Non-Magnetic	No

Contact Features

Contact Type	Socket
	10 µin



Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Brass
D-Sub Contact Size	20
Contact Current Rating (Max)	5 A

Termination Features

Termination Post Length	3.95 mm[.156 in]
-------------------------	------------------

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Dimensions

Post Diameter	.76 mm[.03 in]
---------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

ULTRA-LITE Connector	No
Circuit Application	Signal

Industry Standards

NASA Qualification	No
--------------------	----

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	For solder dip product see part number 443975-7.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2022  
(223)  
Candidate List Declared Against: JAN 2021  
(211)  
SVHC > Threshold:  
Cd (1.5%)

Article Safe Usage Statements:  
Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.


Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

 <p>TE Part #205558-2 AMPLIMITE,ASY,PLUG,STD,109,2</p>	 <p>TE Part #1617037-9 HFW5A1201K00 = HFW 5AMP RELAY</p>	 <p>TE Part #103957-4 4X5 MTE RCPT SR LATCH .100CL</p>	 <p>TE Part #1218124-4 37 POS,ASSY,PLUG,LOW PROF,109</p>
 <p>TE Part #1218124-1 9 POS,ASSY,PLUG,LOW PROF,109</p>	 <p>TE Part #1218124-3 25 POS,ASSY,PLUG,LOW PROF,109</p>	 <p>TE Part #1218124-5 50 POS,ASSY,PLUG,LOW PROF,109</p>	 <p>TE Part #443975-1 AMPLIMITE,RCPT ASY,POSTD,109,1</p>



TE Part #443975-5  
AMPLIMITE,RCPT ASY,POSTD,109,5



TE Part #YDIV46E11-35SNV001  
PLUG ASSY

Documents

Product Drawings

AMPLIMITE,RCPT ASY,POSTD,109,2

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_443975-2\_F.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_443975-2\_F.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_443975-2\_F.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_443975-2\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_443975-2\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_443975-2\_C.3d\_stp.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English