

316370-6

AMP | Multilock Connector System

TE Internal #: 316370-6


TE Internal Description: 040 II SRS MK-II 48P CAP ASSY

High Pin Count Header

[View on TE.com >](#)



Automotive Parts > Automotive Connectors > Automotive Headers > High Pin Count Header



PCB Mount Orientation: **Horizontal**

Termination Method to PCB: **Through Hole - Screw**

Sealable: **No**

Centerline (Pitch): **2.5 mm, 3.5 mm [.098 in, .138 in]**

Connector System: **Wire-to-Board**

[All High Pin Count Header \(43\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Mixed & Hybrid Header	No
Header Type	Fully Shrouded
Connector Shape	Rectangular
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	48
Number of Sections	2
PCB Mount Orientation	Horizontal
Number of Positions	48
Number of Rows	3

Electrical Characteristics

Operating Voltage	12 VDC
Voltage Rating (Max)	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Primary Product Color	Light Gray
-----------------------	------------

Contact Features

Mating Tab Width	1 mm[.039 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Type	Tab
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Through Hole - Screw
---------------------------	----------------------

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
PCB Mount Retention	Without
Mounting Holes	With
PCB Mount Retention Type	Mounting Hole
Mating Alignment	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.5 mm, 3.5 mm[.098 in][.138 in]
--------------------	----------------------------------

Dimensions

Connector Width	72.5 mm[2.85 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Length	17.7 mm[.69 in]
Profile Height from PCB	19.9 mm[.78 in]

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Solder Process	Reflow Solder Capable
Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Quantity	30
Packaging Method	Tray

Other

Interface Number	316372
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Multilock Connector System



Customers Also Bought





TE Part #174960-2
20POS,TAB1.8X0.64,HDR ASSY,
180DEG

Documents

Product Drawings

040 II SRS MK-II 48P CAP ASSY

Japanese

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_316370-6_C4.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_316370-6_C4.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_316370-6_C4.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_316370-6_G.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_316370-6_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_316370-6_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

040II/070II Multi Lock Connector MK-II Type

Japanese

[Product Specification](#)



Japanese