

Single medium lapped screen cable



Part NO: RGW-1647

Product Code: Single medium lapped screen cable

Product Description

Application:

For communication and signal control systems.

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

1

Cable Construction

Conductor	Bare Copper
Construction	0.1±0.005x18
Stranded Dia.(±0.015mm)	0.49
Insulation	PE
Thickness	0.3
Insulation Dia.(±0.1mm)	1.10
Insulation Color	Red

Spiral	Bare Copper
Construction (mm)	0.10±0.003×33
coverage	95%
Jacket	PVC
Thickness(mm)	>=0.3
Dia.(±0.15mm)	1.90
Jacket Color	Grey (RAL7001)

Marking

No Marking

PACKAGING


100M/Reel 25M/Reel

RoHS GUIDELINE			
We operate according to the following standards			
Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	/
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	/

Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	132
Min.Insulation DC Resistance at 20°C (MΩ *Km)	>500
Rated Temperature(°C)	-20 to +60
Rated Voltage(V)	30
Capacitance(pF/m)	160

Label on Reel

Product label

Single medium lapped screen cable

Grey

100M

RoHS(2002/95/EC) Compliant

WW/YY

RS label

7492554
100M
Made in China



7492550
25M
Made in China



Date: 2011-09-13

Page: 1 / 1