

COAXIAL ADAPTER, SMA-26.5GHz, 50 Ohm, jack / jack (female / female)

31_SMA-50-0-100/111_N

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
SMA-26.5GHz	jack (female)	HUBER+SUHNER-SMA-26.5GHz
SMA-26.5GHz	jack (female)	HUBER+SUHNER-SMA-26.5GHz

Interface and material data		
SMA-26.5GHz		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
SMA-26.5GHz		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body		Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	26.5 GHz

Mechanical data	
Weight	0.006 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 125 °C

COAXIAL ADAPTER, SMA-26.5GHz, 50 Ohm, jack / jack (female / female)

31_SMA-50-0-100/111_N

Ordering Information Table		
Item number	Item description	Packaging type
22648729	31_SMA-50-0-100/111_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2369 / Date of publication: 14.02.2024 / uncontrolled copy