







FEMALE END VIEW	BOARD LAYOUT	TYPICAL PANEL CUTOUT	SPECIFICATIONS																	
			<table border="1"> <tr><td>CONTACT CARRIER MATERIAL</td><td>TPU</td></tr> <tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr> <tr><td>RATED CURRENT [A]</td><td>4.0 A</td></tr> <tr><td>RATED VOLTAGE [V]</td><td>250 V</td></tr> <tr><td>HOUSING/LOCKNUT MATERIAL</td><td>BRAS/NICKEL</td></tr> <tr><td>NUMBER OF CONDUCTORS [AWG]</td><td>5 PRINTED CIRCUIT PINS</td></tr> <tr><td>TEMPERATURE RATING</td><td>-40°C to +80°C (-40°F to +176°F)</td></tr> <tr><td>PROTECTION CLASS</td><td>MEETS NEMA 1,3,4,6P AND IEC IP68</td></tr> </table>	CONTACT CARRIER MATERIAL	TPU	CONTACT MATERIAL/PLATING	BRASS/GOLD	RATED CURRENT [A]	4.0 A	RATED VOLTAGE [V]	250 V	HOUSING/LOCKNUT MATERIAL	BRAS/NICKEL	NUMBER OF CONDUCTORS [AWG]	5 PRINTED CIRCUIT PINS	TEMPERATURE RATING	-40°C to +80°C (-40°F to +176°F)	PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68	
CONTACT CARRIER MATERIAL	TPU																			
CONTACT MATERIAL/PLATING	BRASS/GOLD																			
RATED CURRENT [A]	4.0 A																			
RATED VOLTAGE [V]	250 V																			
HOUSING/LOCKNUT MATERIAL	BRAS/NICKEL																			
NUMBER OF CONDUCTORS [AWG]	5 PRINTED CIRCUIT PINS																			
TEMPERATURE RATING	-40°C to +80°C (-40°F to +176°F)																			
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68																			



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	<div style="text-align: right;"> <b>TURCK INC</b>  <i>High Technology Sensors and Automation Controls</i> </div> <div style="text-align: right;">         3000 CAMPUS DRIVE          MINNEAPOLIS, MN 55441          1-800-544-7769          (763) 553-7300          (763) 553-0708 fax          turck.com       </div>
MATERIAL  SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT DF DATE 12/11/98 APVD DF SCALE 1=.7	DESCRIPTION  FKFDKW 4.5
FINISH  SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b>  DO NOT SCALE THIS DRAWING	IDENTIFICATION NO. U4506 REV F FILE: U4506 SHEET 1 OF 1

F	DRAWING PROCESSED AS PART OF ECO 33971	CBM	04/07/11	33971
REV	DESCRIPTION	BY	DATE	ECO NO.