

	Part Number	Thermal Resistance °C/W at 3in length	Width in	Height in	Surface Area in ² in	Weight lb/ft	Part Class
	63730	1.88	3.00	2.25	37.1	2.90	A




Thermal Curves
based on 3.000 in length

Natural Convection

Heat Sink Temperature Rise Above Ambient




Heat Sink Thermal Resistance




Forced Convection

Heat Sink Temperature Rise Above Ambient (10W Dissipated)



Heat Sink Thermal Resistance



Building a Part Number

Full Bar Length = 8.00ft

Base Part #	Bar Length	Finish	Length (use zeros for full or half bars)
63730	1 Full	F Unfinished	0 0 0 0
	2 Half	F Unfinished	0 0 0 0
	3 Custom	B Black Anodized C Gold Chromate U* Unfinished	indicate length <i>in inches</i> to three decimal places; 1 5 2 5 0 = 15.250 "