

LS-EMLP (148X55) WH - Device marker



1322595

<https://www.phoenixcontact.com/in/products/1322595>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 3, text field height: 55 mm, text field width: 148 mm



Your advantages

- Stick-on device marking
- Prefabricated device markers in the proven laser-sheet format for ideal positioning in the marking device
- Very high contrast due to the white top layer with black marking

Commercial data

Item number	1322595
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	*****
Product key	BG241D
GTIN	4063151607180
Weight per piece (including packing)	40.1 g
Weight per piece (excluding packing)	39 g
Customs tariff number	39203000
Country of origin	DE

Technical data

Product properties

Product type	Device marking
Type	Laser sheet

Marking

Number of individual labels	3
Identification technology	Direct laser marking

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	ABS
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	148 mm
Text field width	148.00 mm
Text field height	55.00 mm
Length	55 mm
Material strength	0.80 mm

LS-EMLP (148X55) WH - Device marker



1322595

<https://www.phoenixcontact.com/in/products/1322595>

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

LS-EMLP (148X55) WH - Device marker



1322595

<https://www.phoenixcontact.com/in/products/1322595>

Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EMLP (148X55) WH - Device marker



1322595

<https://www.phoenixcontact.com/in/products/1322595>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

LS-EMLP (148X55) WH - Device marker



1322595

<https://www.phoenixcontact.com/in/products/1322595>

Accessories

TOPMARK NEO - Laser marker

1012015

<https://www.phoenixcontact.com/in/products/1012015>



Laser marking system for the efficient marking of metal or plastic marking material from the LS..., UCT..., UC.../PP..., UM... product families.

TMN-ADAPTER PLATE-LS - Adapter plate

1012104

<https://www.phoenixcontact.com/in/products/1012104>



Adapter plate for LS materials incl. 4 magnets for spot securing of lightweight marking materials

LS-EMLP (148X55) WH - Device marker

1322595

<https://www.phoenixcontact.com/in/products/1322595>



TMN-FRAME-LS - Holding plate

0803478

<https://www.phoenixcontact.com/in/products/0803478>

Retaining plate for circumferentially securing lightweight marking materials




TOPMARK LASER-MAG SHEET - Magazine

0831836

<https://www.phoenixcontact.com/in/products/0831836>

Sheet magazine for TOPMARK LASER



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in