

SPECIFICATIONS:

ELECTRICAL:

INSULATION RESISTANCE:

DIELECTRIC WITHSTANDING VOLTAGE:

5 GOhms MIN. 1000 VAC FOR 1 MIN

WORKING VOLTAGE:

250V

OPERATING TEMPERATURE:

-55°C TO +125°C

POWER CONTACT RESISTANCE: 2.0 mOhms MAX. POWER CONTACT AMPERAGE: SEE P/N KEY

MECHANICAL:

4.5 Kg MAX. CONTACT INSERTION FORCE: 0.3 Kg MIN. CONTACT SEPARATION FORCE:

MATERIALS:

CONTACTS: COPPER ALLOY, GOLD FLASH

INSULATOR:

230°C PROCESS TEMP.

SHELL: HARDWARE: NICKEL PLATED STEEL NICKEL PLATED BRASS

PBT UL94V-0 RATED

681M3W3K103LYYY

0 = 40 AMP POWER // STANDARD PCB TAILS

1 = 40 AMP POWER // 2.22mm PCB TAILS 2 = 20 AMP POWER // STANDARD PCB TAILS

0 = NO HARDWARE

1 = 0.098" CN PCB SIDE

2 = 0.236" CN PCB SIDE

3 = 0.236" CN MATING SIDE 4 = 0.237" BOARDLOCK PCB SIDE

5 = 0.224" BOARDLOCK PCB SIDE

1 = GOLD FLASH -

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DESCRIPTION: POWER - VERTICAL - MALE - MACHINED

DRAWN: M. SIGMON

DATE: 07/19/2013 UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET NTS DWG NO.


3 681M3W3K103LYYY


REV

OF

1

DESCRIPTION: POWER - VERTICAL - MALE - MACHINED





RoHS COMPLIANT

例

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:

07/19/2013

UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp

681M3W3K103LYYY

3


REV


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS


TOLERANCE:

ALL DIMENSIONS ARE ±0.010


0 NO HARDWARE









4 0.237" PCB SIDE




1 0.098" PCB SIDE



3 0.236" MATING SIDE



5 0.224" PCB SIDE



ROHS COMPLIANT



DRAWN: M. SIGMON

DATE: 07/19/2013 UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET 3 NTS 3 DWG NO.

681M3W3K103LYYY

REV