

RC unit for 5SY, 4-pole, type AC, In: 63 A, 300 mA, Un AC: 400 V



Figure similar

Model	
product brand name	SETRON
product designation	RCD-unit
design of the product	Instantaneous
product type designation	5SM2
product variations	for 5SY
General technical data	
number of poles	4
design of pole	4 poles
size of installation devices according to DIN 43880	1
touch protection against electrical shock according to EN 50274	Finger and back-of-hand safe
mechanical service life (operating cycles) typical	10 000
overvoltage category	III
degree of pollution	2
Voltage	
type of voltage of the operating voltage	AC
insulation voltage (Ui) rated value	460 V
surge voltage resistance rated value	4 000 V
tripping fault current rated value	300 mA
operational current	
• at 40 °C rated value	58.6 A
• at 45 °C rated value	58.59 A
• at 50 °C rated value	56.7 A
• at 55 °C rated value	54.81 A
• at 60 °C rated value	53.55 A
• at 65 °C rated value	52.29 A
• at 70 °C rated value	50.4 A
• at AC rated value	63 A
residual current type	AC
supply voltage	
• at AC	400 V
• for testing equipment minimum	195 V
value range of the supply voltage frequency	50 Hz
value range of the operating frequency	50 Hz
Protection class	
protection class IP	IP20, if the distribution board is installed, with connected conductors
protection function false tripping	Yes
Dissipation	

power loss [W] • for rated value of the current at AC in hot operating state per pole • maximum	3 W
	9 W

Product details	
product feature • OFF-delay time adjustable • rated fault current adjustable • sealable	No
	No
	No
	No

Connections	
connectable conductor cross-section solid • minimum • maximum	1.5 mm²
	25 mm²
connectable conductor cross-section stranded • minimum • maximum	1.5 mm²
	25 mm²
tightening torque with screw-type terminals • minimum • maximum	2.5 N·m
	3 N·m
position of power supply cord	top or bottom

Mechanical Design	
height	90 mm
width	124 mm
depth	77 mm
installation depth	70 mm
number of modular width units	3
fastening method	REG
mounting position	any
net weight	312 g

Environmental conditions	
ambient temperature during operation • minimum • maximum	-5 °C
	45 °C
ambient temperature during storage • minimum • maximum	-40 °C
	75 °C
number of test cycles for environmental testing according to IEC 60068-2-30	28

Certificates	
reference code according to IEC 81346-2	F

Approvals Certificates	
General Product Approval	



[Confirmation](#)



General Product Approval	other	Dangerous goods	Environment
Miscellaneous	Miscellaneous	Confirmation	Transport Information
		Environmental Confirmations	
Environment			
Environmental Confirmations			

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SM2645-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SM2645-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM2645-0


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

7/5/2024 

