

# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, straight, M23, M23, number of positions: 5+PE, contact connection type: Socket/pin, Axial O-ring, 4xM3, shielded: yes, cable diameter range: 0 mm ... 0 mm, number of positions: 6, connection method: Crimp connection, series: SF, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1241893       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | *****         |
| Product key                          | ABRBFJ        |
| GTIN                                 | 4063151397746 |
| Weight per piece (including packing) | 186.222 g     |
| Weight per piece (excluding packing) | 186.222 g     |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>

## Technical data

### Notes

#### Safety note

##### Safety note

WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.

- WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.

- WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.

- The products are suitable for applications in plant, controller, and electrical device engineering.

- When operating the connectors in outdoor applications, they must be separately protected against environmental influences.

- Assembled products may not be manipulated or improperly opened.

- Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at [phoenixcontact.com/products](https://www.phoenixcontact.com/products)).

- When using the product in direct connection with third-party manufacturers, the user is responsible.

- For operating voltages > 50 V AC, conductive connector housings must be grounded

- Ensure that the protective or functional ground has been properly connected.

- VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector

- Only use tools recommended by Phoenix Contact

- The installation notes/Design In documents online on the download page at [phoenixcontact.com/products](https://www.phoenixcontact.com/products) must be observed for this product.

- Operate the connector only when it is fully plugged in and interlocked.

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.

- Observe the minimum bending radius of the cable. Lay the cable without twisting it.

- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>

## Mounting

|          |       |
|----------|-------|
| Mounting | 4x M3 |
|----------|-------|

## Product properties

|                     |                                   |
|---------------------|-----------------------------------|
| Product type        | Circular connectors (device side) |
| Series              | SF                                |
| Application         | Power                             |
| Number of positions | 6                                 |
| Connection profile  | 5+PE                              |
| Shielded            | yes                               |
| Coding              | N                                 |
| Thread type         | M23                               |

## Material specifications

|               |     |
|---------------|-----|
| Seal material | FPM |
|---------------|-----|

## Electrical properties

### Contact

|                       |       |
|-----------------------|-------|
| Max. current          | 30 A  |
| Nominal voltage $U_N$ | 630 V |
| Overvoltage category  | III   |
| Degree of pollution   | 3     |
| Rated surge voltage   | 6 kV  |

### Contact

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

## Connection data

### Conductor connection

|                         |                  |
|-------------------------|------------------|
| Connection method       | Crimp connection |
| Contact connection type | Socket/pin       |

## Connector

|      |          |
|------|----------|
| Type | straight |
|------|----------|

### Connection 1

|             |        |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

### Connection 2

|             |      |
|-------------|------|
| Head design | Plug |
|-------------|------|

## Cable/line

|                         |               |
|-------------------------|---------------|
| External cable diameter | 0 mm ... 0 mm |
|-------------------------|---------------|

# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>


## Environmental and real-life conditions

### Ambient conditions

|                                          |                   |
|------------------------------------------|-------------------|
| Degree of protection                     | IP67              |
| Ambient temperature (operation)          | -40 °C ... 125 °C |
| Ambient temperature (storage/transport)  | 15 °C ... 25 °C   |
| Altitude                                 | 3000 m            |
| Permissible humidity (storage/transport) | 50 % ... 65 %     |


## Drawings

Schematic diagram



Pin assignment of pin

Diagram



I = current strength, T = ambient temperature


# SF-5EE1N8AS000X - Panel feed-through

1241893

<https://www.phoenixcontact.com/in/products/1241893>




Schematic diagram



Socket pin assignment

Dimensional drawing



Installation dimensions

# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1241893>

|                                                                                                                                          |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>cUL Recognized</b><br>Approval ID: E153698-20041116 |                       |                       |                   |                             |
|                                                                                                                                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                          | 600 V                 | 18 A                  | 12                | -                           |

|                                                                                                                                         |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>UL Recognized</b><br>Approval ID: E153698-20041116 |                       |                       |                   |                             |
|                                                                                                                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                         | 600 V                 | 27 A                  | 12                | -                           |

|                         |  |  |  |  |
|-------------------------|--|--|--|--|
| <b>cULus Recognized</b> |  |  |  |  |
|-------------------------|--|--|--|--|

# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|



# SF-5EE1N8AS000X - Panel feed-through



1241893

<https://www.phoenixcontact.com/in/products/1241893>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

# SF-5EE1N8AS000X - Panel feed-through

1241893

<https://www.phoenixcontact.com/in/products/1241893>



## Accessories

### SF-Z0019 - Protective cap

1607449

<https://www.phoenixcontact.com/in/products/1607449>



Plastic protection cap, with eye, IP40 for connectors with M23 external thread, RF, SF series

---

### SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>



Torque screwdriver, series: RC, UC, SH, SF

## SF-5EE1N8AS000X - Panel feed-through

1241893

<https://www.phoenixcontact.com/in/products/1241893>



## SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>



Hook wrench, series: RC, UC, RF, SF

---

## PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>



Plastic protective cap, M23, series: M23 PRO

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)