


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		K2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



CONTACT IDENTIFICATION LETTER "D" (LOCATED IN THIS AREA)

HOUSING (SEE TABLE FOR PART NO.)

POSITION #1 INDICATOR

- 1 CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2 USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3 THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103661
- 6 ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7 MATERIAL- HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK
PINS: PHOS. BRONZE
- 8 FINISH- PINS: .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 9 FINISH- PINS: .000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
- 10 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 11 FINISH- PINS: .000100-.000200 MATTE TIN OVER .000050 NICKEL.
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

12	OBSOLETE	11	2	2.59	1.295	1-103653-1	12	6-103944-1
12	OBSOLETE	11	2	2.39	1.195	1-103653-0	11	6-103944-0
		11	2	2.19	1.095	103653-9	10	5-103944-9
		11	2	1.99	.995	103653-8	9	5-103944-8
		11	2	1.79	.895	103653-7	8	5-103944-7
		11	3	2.39	.795	103653-6	7	5-103944-6
		11	2	1.39	.695	103653-5	6	5-103944-5
		11	4	2.38	.595	103653-4	5	5-103944-4
		11	4	1.98	.495	103653-3	4	5-103944-3
		11	5	1.98	.395	103653-2	3	5-103944-2
		11	8	2.36	.295	103653-1	2	5-103944-1
		10	3	2.39	.795	103653-6	7	1-103944-3
		10	4	1.98	.495	103653-3	4	1-103944-2
		8	2	2.59	1.295	1-103653-1	12	1-103944-1
12	OBSOLETE	8	2	2.39	1.195	1-103653-0	11	1-103944-0
		8	2	2.19	1.095	103653-9	10	103944-9
		8	2	1.99	.995	103653-8	9	103944-8
		8	2	1.79	.895	103653-7	8	103944-7
		8	3	2.39	.795	103653-6	7	103944-6
		8	2	1.39	.695	103653-5	6	103944-5
		8	4	2.38	.595	103653-4	5	103944-4
		8	4	1.98	.495	103653-3	4	103944-3
		8	5	1.98	.395	103653-2	3	103944-2
		8	8	2.36	.295	103653-1	2	103944-1
PLATING		6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN R.BROWN 26JUL00
 CHK K.WRIGHT 26JUL00
 APVD K.WRIGHT 26JUL00

DIMENSIONS: INCHES
 TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -

MATERIAL 7
 FINISH SEE TABLE

PRODUCT SPEC 108-25034
 APPLICATION SPEC 114-25026
 WEIGHT -

NAME SHROUDED PIN ASSY, AMPMDO MTE, SINGLE ROW, .100 CL, POLARIZED, W/ LATCH WINDOWS, FOR NO 22-NO 26 AWG WIRE SIZE, STRIP FORM

SIZE A2 CAGE CODE 00779 DRAWING NO C=103944 RESTRICTED TO -

CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 1 REV K2

TE Connectivity