

Project..... Comments.....

Fixture Type..... Prepared By.....

Product Description:

Registered Community Design - 001861261. IP65 high power LED fire rated downlight. Integrated LED driver connected to loop-in / loop-out FASTFIX connector (included). Tested in 30, 60 & 90 minute fire rated ceilings. Tested to BS476 Part 21. Tested to BS EN ISO 140-3:1995 & BS EN ISO 140-6:1998 (Acoustics) confirming that they maintain the ability for an internal or separating floor to provide sound insulation. Dimmable (AU-FRLD911, AU-FRLD913) and non-dimmable (AU-FRL901, AU-FRL903) versions available (dimmable with leading/trailing edge).

Product Image & Dimensions:



Overall Diameter 88 mm

Product Specifications:

- Input Voltage (Min): 220 V
- Input Voltage (Max): 240 V
- Input Voltage Type: AC
- Dimmable: Yes
- Beam Angle: 40 °
- IP Rating: IP65
- Lifespan: 75000 hrs
- No. of LEDs: 3
- Cutout Diameter: 65-72 mm
- Recess Depth: 105 mm
- Overall Diameter: 88 mm
- Guarantee: 7 Years

Compliance & Approvals:



SKU Table and Ordering:

SKU Code	Wattage	Colour Temperature	Lumens	Finish Colour	EAN	Qty
AU-FRLD913W/30	9 W	3000 K	410 lm	White	5055155474683	<input type="text"/>
AU-FRLD913W/40	9 W	4000 K	415 lm	White	5055155474690	<input type="text"/>

Warranty:

For available warranty information for this product, please visit:

<http://gb.auroralighting.com/Products/Indoor-Luminaires/Commercial-Lighting/LED-High-Bays/Light-Engines/90-305V-AC-150W-LED-High-Bay.aspx>

UK Sales

16 Alban Park
Hatfield Road, St. Albans
United Kingdom
PH: +44 (0) 1727 83 66 11
FX: +44 (0) 1727 83 66 22

UK Distribution

Apex Park, 6 Little Burrows
Burrowfields, Welwyn Garden City
AL7 4SW
United Kingdom
PH: +44 (0) 1707 35 18 20
FX: +44 (0) 1727 35 18 21