

Product datasheet

Specifications



circuit breaker ComPacT NSXm H
(70 kA at 415 VAC), 3P 3d, 50 A
rating Micrologic 4.1 trip unit,
EverLink connectors

C11H34V050L

EAN Code: 3606481993014

Main

Range	ComPacT
product name	ComPacT NSXm
Range of product	ComPacT NSXm
Device short name	NSXm 63H
Product or component type	Earth leakage circuit breaker
Device application	Distribution
Poles description	3P
Protected poles description	3D
[In] rated current	50 A at 40 °C
[Ue] rated operational voltage	440 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	100 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 660...690 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	H 70 kA 415 V AC
Trip unit name	MicroLogic 4.1
Trip unit technology	Electronic
Trip unit protection functions	LSolR
control type	Toggle
Circuit breaker mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV

[Ics] rated service short-circuit breaking capacity	100 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 70 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 30 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 22 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 2.5 kA at 660...690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	20000 cycles
Electrical durability	20000 cycles at 440 V In/2 10000 cycles at 440 V In 10000 cycles at 690 V In/2 5000 cycles at 690 V In
Power dissipation per pole	1.2 W
Mounting support	Backplate
Mounting position	Horizontal and vertical Flat on the back
Upside connection	Front
Downside connection	Front
Connection terminals	1 Everlink lug wire size 2.5...70 mm ² , fine stranded copper 1 Everlink lug wire size 2.5...95 mm ² , rigid or stranded aluminium/copper
Connection pitch	35 mm with spreaders 27 mm without spreaders
9 mm pitches	9 module
Trip unit rating	50 A at 40 °C
Long-time pick-up adjustment type Ir (thermal protection)	Adjustable 9 settings
[Ir] long-time protection pick-up adjustment range	20...50 A
Long-time protection delay adjustment type tr	Fixed
[tr] long-time protection delay adjustment range	200 s at 1.5 x Ir 8 s at 6 x Ir 5 s at 7.2 x Ir
Thermal memory	20 minutes before and after tripping
Short-time protection pick-up adjustment type Isd	Adjustable 9 settings
[Isd] Short-time protection pick-up adjustment range	1.5...10 x Ir
Short-time protection delay adjustment type tsd	Fixed
Instantaneous protection pick-up adjustment type Ii	Fixed
[Ii] instantaneous protection pick-up adjustment range	750 A
Earth-leakage protection	Integrated
Earth-leakage protection class	Class A Class AC
Earth-leakage protection sensitivity adjustment type IΔn	Adjustable
[IΔn] earth-leakage protection sensitivity adjustment range	30 mA 100 mA 300 mA 500 mA 1 A 3 A 5 A

Earth-leakage sensitivity	30 mA for class A 100 mA for class A 300 mA for class A 500 mA for class A 1 A for class A 30 mA for class AC 100 mA for class AC 300 mA for class AC 500 mA for class AC 1 A for class AC 3 A for class AC 5 A for class AC
Earth-leakage protection time delay adjustment type Δt	Adjustable
[Δt] Earth-leakage protection time delay adjustment range	0 ms 60 ms 150 ms 500 ms 1000 ms
Number of slots for electrical auxiliaries	1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX
Local signalling	Flag (green) for presence of auxiliary contacts
Width (W)	108 mm
Height (H)	144 mm
Depth (D)	80 mm
Net weight	1.63 kg
Colour	Grey (RAL 7016)

Environment

Standards	EN/IEC 60947
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	0...95 %
Operating altitude	2000 m without derating 5000 m with derating

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.000 cm
Package 1 Width	16.000 cm
Package 1 Length	19.000 cm
Package 1 Weight	1.706 kg
Unit Type of Package 2	S03
Number of Units in Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm

Package 2 Length	40.000 cm
Package 2 Weight	7.244 kg
Unit Type of Package 3	P12
Number of Units in Package 3	32
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	69.952 kg

Logistical informations

Country of origin	PL
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) 53

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Recycled metal content at CR level 0

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant with Exemptions

SCIP Number Af3d4202-1697-430d-83ec-d7a972ac0ddb

REACH Regulation [REACH Declaration](#)

Halogen content performance Halogen free plastic parts product

PVC free Yes

Silicon free No

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)


Take-back No

WEEE  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Offer Marketing Illustration

Product benefits / Features

CompacT NSXm Technical Features



Offer Marketing Illustration

Product benefits / Features



Compact NSXm
Range Accessories

Wireless indication auxiliary

Long terminal shield

Standard auxiliary contact

Rotary handles

Inter-phase barrier

Toggle padlocking device

MN undervoltage release

Standard MX shunt release

The image displays a collection of accessories for the Compact NSXm circuit breaker range. At the top left, a green circular graphic contains a small image of the main circuit breaker. Below this, the title 'Compact NSXm Range Accessories' is shown in green and black text. The accessories are arranged in three rows. The first row includes a green wireless indication auxiliary, a long terminal shield, and a standard auxiliary contact. The second row features rotary handles and an inter-phase barrier. The third row contains a toggle padlocking device, an MN undervoltage release, and a standard MX shunt release. Each accessory is accompanied by a small image and a descriptive label.

Offer Marketing Illustration

Product benefits / Features

CompacT NSXm Moulded Case Circuit Breaker



Efficiency

It features integrated earth leakage protection and standardized accessories – which means you save space, time, and effort.



Reliability

optimized in size and featuring innovations tailored to your needs. Roto-active™ breaking technology helps to increase operation lifespan.



Connectivity

Designed to connect to EcoStruxure Power, an IoT-connected architecture for improving every aspect of your power distribution system.



Offer Marketing Illustration

Product benefits / Features



Compact NSX Technical Benefits

- Come in one size and are optimized for small spaces.
- 3 or 4 pole versions
- Rated currents: 16 to 160 A
- Thermal-magnetic protections
- Breaking capacities under 240/415 V
16, 25, 36, 50, 70 kA
- Integrated earth leakage protection via MicroLogic Vigi (earth leakage circuit breaker - ELCB)
- EverLink™ connectors for bare cables

Technical Illustration

Assembly's dimensions

