



BEDROCK 3D PLA Tough

Fast. Tough. Biocompatible. Easy to Print.

Technical Documentation Sheet

version 1.0





Technical Data Sheet

PLA TOUGH

Fast. Tough. Biocompatible. Easy to Print.

BEDROCK 3D PLA TOUGH is the ultimate choice for fast, easy, sustainable, cost- and time-saving production of various applications. This is a one stop material. Great aesthetics, on all printers and for all sizes, PLA Tough does it without compromises.

Filament Properties

Filament Diameter	1.75 mm	2.85 mm
Average diameter Tolerance	±0.050 mm	±0.1 mm
Average ovality	<0.050 mm	<0.050 mm
Available Spool size	750 g, 2.0 kg, 4.0 kg, 8.0 kg	750 g, 2.0 kg, 4.0 kg, 8.0 kg
Available colors	Natural, Black	

Spool Properties

Spool size	750 g	2.0 kg	4.0 kg	8.0 kg
Outer diameter	200 mm	300 mm	350 mm	355 mm
Inner diameter	50.5 mm	51.5 mm	51.7 mm	36 mm
Width	55 mm	103 mm	103 mm	167 mm

Recommended 3D-Print processing parameters

Used for test specimens

Printer	FFF printer	Ultimaker S5
Nozzle Temperature ¹⁾	200 – 220 °C / 392 – 428 °F	220 °C / 428 °F
Build Chamber Temperature	-	Indirect heating (cover)
Bed Temperature	50 – 70 °C / 122 – 158 °F	60 °C / 140 °F
Bed Material	Glass	Glass

¹ Fast printing might require an additional increase of the nozzle temperature; the stated printing speed is based on current validations. As equipment and technology continues to evolve, it is possible that even higher printing speeds may be attainable in the future.



Nozzle Diameter	≥ 0.4 mm	0.4 mm
Print Speed	40 – 300 mm/s ¹	40 mm/s
Max Volumetric Speed ²⁾	21 mm ³ /s	//

Please check your standard and/or high speed print profile availability for an easy start at www.bedrock3d.com.

Annealing Recommendations for Performance Enhancement

Equipment	Use an oven which can heat up to ~120°C.	
Part preparation	Place the parts inside the oven. Fix larger parts to avoid potential deformation during the annealing process.	
Annealing Process ³⁾	Heating	From room temperature to 120°C / 248 °F in ~15 min (ramp up time).
	Holding the temperature	120°C / 248 °F for 30 min (thicker parts might require a longer time).
	Cooling	From 120°C / 248 °F to room temperature in ~15 min (ramp down time).

Further Recommendations

Drying recommendations to ensure printability and best mechanical properties ⁴⁾	BEDROCK 3D PLA Tough is in a printable condition, drying is not necessary
Support material compatibility	Single material breakaway, BEDROCK 3D BVOH
Warehousing	BEDROCK 3D PLA Tough filament should be stored at 15 - 25°C in its originally sealed package in a clean and dry environment. If the recommended storage conditions are observed the products will have a minimum shelf life of 12 months.

General Properties	Standard	Average Values
--------------------	----------	----------------

² Based on Bambu Lab X1C with a nozzle diameter of 0.4 mm

³ The annealing process can lead to a minor deviation in the dimensional accuracy. It is observed for the cross section of DIN EN ISO 527 Type 1A tensile bars minor deviation of up to +2% in thickness (nominal value 4 mm) and -1% in width (nominal value 10 mm).

⁴ Please note: To ensure constant material properties the material should always be kept dry.



Filament Density⁵⁾ ISO 1183-1 1215 kg/m³

Tensile Properties ⁶⁾	Standard	Average Values		
		XY-Direction	XZ-Direction	ZX-Direction
Tensile strength ⁷⁾	ISO 527	40 MPa	-	28 MPa
Elongation at Break ⁷⁾	ISO 527	7.4%	-	2.5%
Young's Modulus ⁸⁾	ISO 527	2672 MPa	-	2576 MPa

Flexural Properties ^{6) 9)}	Standard	Average Values		
		XY-Direction	XZ-Direction	ZX-Direction
Flexural Strength	ISO 178	73 MPa	75 MPa	51 MPa
Flexural Modulus	ISO 178	2690 MPa	2410 MPa	2390 MPa
Flexural Elongation at Break	ISO 178	No break	No break	3.1%

Impact Properties ⁶⁾	Standard	Average Values		
		XY-Direction	XZ-Direction	ZX-Direction
Impact Strength Charpy (notched)	ISO 179-2	18 kJ/m ²	8.6 kJ/m ²	2.5 kJ/m ²
Impact Strength Charpy (unnotched)	ISO 179-2	33 kJ/m ²	34 kJ/m ²	10 kJ/m ²
Impact Strength Izod (notched)	ISO 180	18 kJ/m ²	7,1 kJ/m ²	2,4 kJ/m ²
Impact Strength Izod	ISO 180	28 kJ/m ²	27 kJ/m ²	10 kJ/m ²

⁵⁾ measured on filament

⁶⁾ Samples were conditioned in standard climate (23°C, 50% RH 72h)

⁷⁾ Testing speed: 5

⁸⁾ Testing speed: 1 mm/min

⁹⁾ Testing speed: 2 mm/min

Measured on milled specimens




(unnotched)

Thermal Properties ⁶⁾	Standard	Average Values
HDT A at 1.8 MPa	ISO 75-2	55 °C
HDT A at 1.8 MPa (annealed)	ISO 75-2	65 °C
HDT B at 0.45 MPa	ISO 75-2	57 °C
HDT B at 0.45 MPa (annealed)	ISO 75-2	94 °C
Vicat softening point at 50 N	ISO 306	59 °C
Vicat softening point at 50 N (annealed)	ISO 306	86 °C
Vicat softening point at 10 N	ISO 306	61 °C
Vicat softening point at 10 N (annealed)	ISO 306	157 °C
Glass Transition Temperature	ISO 11357-2	62 °C
Melting Temperature	ISO 11357-3	172 °C
Melt Volume-Flow Rate (MVR)	ISO 1133	5.31 cm ³ /10 min (210 °C, 2.16 kg)
Melt Mass-Flow Rate (MFR)	ISO 1133	5.68 g/10 min (210 °C, 2.16 kg)
Coefficient of Thermal Expansion	ISO 11359-2	55 °C


Print direction explanation

The orientation of the 3D printed part in the printer is always aligned with the longest axis first. The print direction is consistently along the Z-axis.





BEDROCK 3D





The data contained in this publication are based on our current knowledge and experience. In view of the many factors that may affect processing and application of our product, these data do not relieve processors from carrying out their own investigations and tests; neither do these data imply any guarantee of certain properties, nor the suitability of the product for a specific purpose. Any descriptions, drawings, photographs, data, proportions, weights etc. given herein may change without prior information and do not constitute the agreed contractual quality of the product. It is the responsibility of the recipient of our products to ensure that any proprietary rights and existing laws and legislation are observed. Values in this document are average values, measured and calculated according to the instructions in the listed standards. The used specimens are produced with the Fused Filament Fabrication method. Measured values can vary depending on used print orientation and print parameters.

Please contact us for further product information, like for example REACH, RoHS, FCS.

The safety data given in this publication is for informational purposes only and does not constitute a legally binding MSDS. The relevant MSDS can be obtained upon request from your supplier or you may contact Forward AM Technologies Netherlands B.V. directly at customerservice@bedrock3d.com

Process materials in a well-ventilated room, or use professional extraction systems.