

CA-12S1N12T008 - Cable connector



1620186

<https://www.phoenixcontact.com/gb/products/1620186>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, angled, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 10 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1244075

Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1620186 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | ABRAEC |
| Product key | ABRAEC |
| Catalog page | Page 92 (C-2-2019) |
| GTIN | 4046356818599 |
| Weight per piece (including packing) | 195.5 g |
| Weight per piece (excluding packing) | 195.5 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-12S1N12T008 - Cable connector



1620186

<https://www.phoenixcontact.com/gb/products/1620186>

Technical data

Product properties

| | |
|------------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Data management status | |
| Article revision | 05 |

Connector

Connection 1

| | |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

Insulating body

| | |
|------------------------------------|--------------------|
| Coding | N |
| Insulation body material | PBT |
| Contact material | CuZn |
| Contact surface material | Ni/Au |
| Insertion/withdrawal cycles | 100 |
| Connection method | Solder connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 12 |
| Direction of rotation | Standard |
| Connection profile | 12 |
| Rated voltage | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Contact diameter | 1 mm |
| Litz wire cross-section | 1 mm ² |
| Nominal current per signal contact | 8 A |

Signal contacts

Signal contacts max.

Housing

| | |
|-----------------------------------|--|
| Housing material | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Type of locking | Screw locking mechanism |
| Pg screw connection | none |
| Degree of protection (plugged in) | IP67 |
| Thread type | M23 |

Seal

| | |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
| Seal material | NBR |

CA-12S1N12T008 - Cable connector



1620186

<https://www.phoenixcontact.com/gb/products/1620186>

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Ambient temperature (storage/transport) | 15 °C ... 25 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 % |

CA-12S1N12T008 - Cable connector


1620186

<https://www.phoenixcontact.com/gb/products/1620186>



Drawings

Schematic diagram



Connector pin assignment

CA-12S1N12T008 - Cable connector





1620186

<https://www.phoenixcontact.com/gb/products/1620186>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1620186>

| | | | | |
|--|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  cUL Recognized Approval ID: E335019-20141210 | | | | |
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 48 V | 6 A | 18 - 18 | - |

| | | | | |
|---|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  UL Recognized Approval ID: E335019-20141210 | | | | |
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 48 V | 8 A | 18 - 18 | - |

| | | | | |
|-------------------------|--|--|--|--|
| cULus Recognized | | | | |
|-------------------------|--|--|--|--|

CA-12S1N12T008 - Cable connector



1620186

<https://www.phoenixcontact.com/gb/products/1620186>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-12S1N12T008 - Cable connector



1620186

<https://www.phoenixcontact.com/gb/products/1620186>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | bacb197f-1a00-4335-b8ca-95de908414fa |

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk