

Eaton 17.5TDMEJ50

Catalog Number: 17.5TDMEJ50

Eaton Bussmann series medium voltage DIN fuse, 50 A, AC 17.5 kV, 2", 51 x 442 mm, backup, DIN, with striker



General specifications

Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	17.5TDMEJ50
	UPC 051712165075
EAN 5027590245999	Product Length/Depth 442 mm
Product Height 54 mm	Product Width 51 mm
Product Weight 2500 g	Warranty Not Applicable
Compliances DIN 43625 VDE 0670-4 IEC 60282-1	Certifications IEC60282-1

Type

Fuse

Application

transformer protection
indoor or outdoor use

Amperage Rating

50 A

Fuse indicator

With Striker

Fuse size

51 x 442 mm

Breaking capacity

50 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Catalogs

17.5TDMEJ50~17-5TDMEJ50~17.5KV 50A 2DIN BROWN RESIN SEAL FUSE

[Bussmann series complete full line catalog no. 1007](#)

Technical data sheets

[720104 12kV DIN medium voltage fuses](#)

[720106 24kV DIN medium voltage fuses](#)

[720105 17.5kV DIN medium voltage fuses](#)

Barrels

1

Used with

270303 Fuse clip

A3354710 Fuse clip

Pre arc (I2T)

2.8 x 1000

Resistance

19.7 Ohms

Watt losses

69 W

Fuse diameter

51 mm

Interrupt rating

50 kAIC

Construction size

51 x 442 mm

Mounting method

Clip-in

Voltage rating

17.5 kV

Fuse type

TDMEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia