



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 5176381-3
PLUG ASS'Y(H) 80P 1.27FHBB

TE Part # 5179656-3
1.27FH PLUG ASS'Y SMT 80P




Customers Also Bought



TE Part #CAT-D9934-A15F
Header Assembly: Wire-to-Board, 5A, gold or tin plated



TE Part #178325-3
DYNAMIC D3100D HDR V 10P ASSY AU076



TE Part #179841-1
AMP POWER D/LOCK T/HDR ASSY 6P



TE Part #1-353082-2
DYNAMIC D-5200 HDR V ASSY 3P




TE Part #CAT-D9934-A66B
DYNAMIC 2000 HDR ASSY



TE Part #5176381-5
PLUG ASS'Y(H) 120P 1.27FHBB



TE Part #5917628-5
REC ASS'Y(V) 120P 1.27FHBB



TE Part #5176381-1
PLUG ASS'Y(H) 40P 1.27FHBB

Documents

Product Drawings

REC ASS'Y(H) 80P 1.27FHBB

English

CAD Files

Customer View Model

ENG_CVM_CVM_5176379-3_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5176379-3_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5176379-3_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.