

Eaton 088705

Catalog Number: 088705

Eaton Moeller® series RMQ16 Indicator light, raised, white Q18LH-WS

General specifications



Product Name	Catalog Number
--------------	----------------

Eaton Moeller® series RMQ16 Indicator light	088705
---	--------

EAN

4015080887058

Product Length/Depth

59 mm

Product Height

18 mm

Product Width

18 mm

Product Weight

0.009 kg

Certifications

CSA File No.: 46552

UL Category Control No.: NKCR

UL

UL 508

CSA Class No.: 3211-03

CSA-C22.2 No. 14-05

IEC/EN 60947-5

CE

CSA

UL File No.: E29184

IEC/EN 60947

Product specifications

Type

Indicator lights

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

Resources

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004136.pdf](#)

[DA-DC-00004158.pdf](#)

Drawings

[eaton-operating-indication-rmq16-indicator-light-dimensions.eps](#)
116C076

[eaton-operating-indication-rmq16-indicator-light-3d-drawing.eps](#)

eCAD model

[DA-CE-ETN.Q18LH-WS](#)

Installation instructions

[IL04716016Z](#)

mCAD model

[DA-CS-leucht_h_18](#)

[DA-CD-leucht_h_18](#)

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Fitted with:

LED W2x4, 6d, max. 30 V, 1 W

Front ring

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Connection to SmartWire-DT

No

Rated impulse withstand voltage (Uimp)

800 V AC

Bezel color

Black

Shock resistance

40 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms

Mechanical, According to IEC/EN 60068-2-27

Bezel material

Plastic

Terminal capacity

0.5 - 1.0 mm²

Lens color

White

Design

Conical

Mounting position

As required

Terminal size

2.8 x 0.8 mm to DIN 46247 and IEC 60760, Fast-on connectors

2.8 x 0.8 mm to DIN 46244, Blade terminal

Overvoltage category

III

Degree of protection

NEMA 1

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

25 °C

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Opening diameter

16 mm

Opening height

16 mm

Rated insulation voltage (U_i)

250 V

Rated operational current for specified heat dissipation (I_n)

0 A

Rated operational voltage (U_e) at AC - max

24 V

Static heat dissipation, non-current-dependent Pvs

0 W

Suitable for number of built-in signal lights

1

Width opening

0 mm

Product category

RMQ16

Size

Front dimensions: 18 x 18 mm

Degree of protection (front side)

IP65

Lens type

High

Square



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia