

8ECF0010.1231C-0

1 General information

- Can be used in cable drag chains
- Assembled specifically for use with ACOPOS P3 servo drives and B&R servo motors
- M12 circular connector - Innovative connector system for fast and secure connections

2 Order data

Order number	Short description	Figure
8ECF0010.1231C-0	EnDat 2.2 cables ACOPOS P3 EnDat 2.2 cable, length 10 m, 1x 4x 0.14 mm ² + 4x 0.35 mm ² , M12 circular connector, 8-pin, A-coded, 8-pin Mini I/O male connector, can be used in cable drag chains	

Table 1: 8ECF0010.1231C-0 - Order data

3 Technical data

Order number	8ECF0010.1231C-0
General information	
Cable cross section	4x 0.14 mm ² + 4x 0.35 mm ²
Durability	Oil resistance per DIN EN 50363-10-2 (VDE 0207-363-10-2) as well as standard cleaning agents and hydraulic oil ¹⁾
Certification	UL AWM Style 20963, 80°C, 30 V, E63216 ¹⁾
Certifications	
CE	Yes
UKCA	Yes
Cable construction	
Supply lines	
Quantity	4
Wire insulation	Special thermoplastic material
Wire colors	White/Green, brown/green, blue, white
Variant	Tinned copper stranded wire
Cross section	0.35 mm ²
Shield	No
Stranding	No
Signal line	
Quantity	4
Wire insulation	Polyolefin foam
Wire colors	Yellow, gray, pink, violet
Variant	Tinned copper stranded wire
Cross section	0.14 mm ²
Shield	No
Stranding	All 4 wires together
Cable stranding	With terminating foil shield
Cable shield	Copper/Tin braiding, optical coverage ≥85%
Outer jacket	
Material	PUR
Color	Green flat
Labeling	B&R 4x0.14 + 4x0.35 FLEX (UL) AWM STYLE 20963 80°C 30 V E63216 ¹⁾
Connector	
Type	8-pin female M12 circular connector, A-coded
Mating cycles	≥500
Contacts	8
Additional connectors	8-pin male Mini I/O encoder connector Mating cycles: <1500 Contacts: 8 Degree of protection per EN 60529: IP30 when connected
Degree of protection per EN 60529	Connected IP65/IP67
Electrical properties ¹⁾	
Operating voltage	≤30 V

Table 2: 8ECF0010.1231C-0 - Technical data

Order number	8ECF0010.1231C-0
Test voltage	
Wire - Wire	1 kV
Wire - Shield	0.5 kV
Conductor resistance	
Supply lines	≤55 Ω/km
Signal line	≤134 Ω/km
Insulation resistance	>200 MΩ*km
Ambient conditions ¹⁾	
Temperature	
Moving	-10°C to 80°C
Static	-40°C to 80°C
Mechanical properties ¹⁾	
Dimensions	
Length	10 m
Diameter	6 mm ±0.2 mm
Bend radius	
Single bend	≥19 mm
Moving	≥47 mm
Drag chain data	
Acceleration	≤6 g
Flex cycles ²⁾	≥3000000
Velocity	≤4 m/s
Weight	0.6 kg


Table 2: 8ECF0010.1231C-0 - Technical data

1) Values refer to the raw cable being used.

2) Valid at an ambient temperature of 20°C and bend radius of 78 mm.

4 Wiring

4.1 Cable construction



Pos.	Name	Note
1	Encoder line	4 x 0.14 mm ² + 4 x 0.35 mm ²
2	8-pin circular connector, A-keyed Contact connector	
3	Heat shrink tubing	
4	Mini I/O encoder connector	

Table 3: 8ECFxxxx.1231C-0 - Cable construction

4.2 Pinout

Circular connector	Pin	Name	Function	Pin	DSUB connector
	8	+12 V out	Encoder power supply +12 V	1	
	3	D	Data input	6	
	4	D\	Data inverted	8	
	7	T	Clock output	2	
	6	T\	Clock output inverted	4	
	1	---	---	---	
	5	COM	Encoder power supply 0 V	7	
	2	---	---	---	

Table 4: M12 circular connector - Pinout

4.3 Cable diagram




Figure 1: 8ECFxxxx.1231C-0 - Cable diagram