

Features

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- A wide range of lubricants are available to meet specific requirements within a temperature range of -60°C to 200°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.

RS PRO Oilite® Plain Bearing

RS Stock No.: 0528187




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

RS PRO is offering range of Oilite® plain bearings - self-lubricating bearings that are made from metal alloys with pores that channel lubricants between the bearing itself and the shaft.

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Lubricant : Shell Tellus S2 MX68
- Temperature range of -15°C to +75°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.
- All dimensions and tolerances of our metric ranges conform to ISO 2795:1991
- Wide range of metric and imperial sizes
- Wide range of different types: Plain, Flanged

* Below dimensions in mm



Specifications

Details

Inner Diameter	0.5625	Outer Diameter	0.6875	Length	0.75
Tolerance Range	Imperial (Inch)				

Material Specification

Structure	Oil impregnated sintered bronze*				
Max PV (N/mm ² x m/s)	1.8	Max Static load (N/mm ²)	50		
Max Dynamic load (N/mm ²)	14	Max Sliding speed (m/s)	5		
Operating temperature (°C)	-60 to 200*	Density (g/cm ³)	6.6		
	*dependant on lubrication				
Radial crushing strength (K Min M/mm ²)	160				

Tolerances & Fittings (Imperial)

	Min	Max	Tolerance
Inside Diameter	0.563	0.564	
Outside Diameter	0.690	0.691	
Overall Length	0.745	0.755	
Concentricity Max	0.003	0.003	

