



Electrical features

Number of poles		4
Rated insulation voltage Ui	V	500
IEC Conventional free air thermal current Ith ≤ 40°C	A	125
Rated peak withstand current Ipk	kA	20
Rated short time current Icw 1s	kA	4.5

Connections

Terminal hole diameter_Option 1	mm	1x9mm
Conductor section connectable_Option 1	mm2	10...35
Tightening torque Max_Option 1	Nm	7
	Ibin	62
Terminal hole diameter_Option 2	mm	3x7.5mm
Conductor section connectable_Option 2	mm2	10...25
Tightening torque Max_Option 2	Nm	2
	Ibin	18
Terminal hole diameter_Option 3	mm	11x5.3mm
Conductor section connectable_Option 3	mm2	2.5...6
Tightening torque Max_Option 3	Nm	2
	Ibin	18


Mechanical features

Operating position	normal allowable	Vertical plane Any
Fixing		Screw / DIN rail 35mm
Phillips		2
Weight	g	515

Resistance & Protection

Terminals IP degree	IP20 front
---------------------	------------

Dimensions



Certifications and compliance

Certifications

IEC/EN/BS 60947-7-1

ETIM classification

EC000066 - Power contactor, AC switching