

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** Bailey

**Supplier's address:** Yvo Hendriks, Everdenberg 21, 4902TT Oosterhout Oosterhout NB, NL

**Model identifier:** 147218

## Type of light source:

|                                                     |      |                                 |     |
|-----------------------------------------------------|------|---------------------------------|-----|
| Lighting technology used:                           | LED  | Non-directional or directional: | DLS |
| Light source cap-type (or other electric interface) | GU10 |                                 |     |
| Mains or non-mains:                                 | MLS  | Connected light source (CLS):   | No  |
| Colour-tuneable light source:                       | No   | Envelope:                       | -   |
| High luminance light source:                        | No   |                                 |     |
| Anti-glare shield:                                  | No   | Dimmable:                       | Yes |


## Product parameters

| Parameter                                                                                                                                             |        | Value                    | Parameter                                                                                                                                                  | Value                  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------|--------|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| General product parameters:                                                                                                                           |        |                          |                                                                                                                                                            |                        |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer                                                                         |        | 3                        | Energy efficiency class                                                                                                                                    | F                      |
| Useful luminous flux ( $\phi_{\text{use}}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) |        | 230 in Narrow cone (90°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 1800...2700            |
| On-mode power ( $P_{\text{on}}$ ), expressed in W                                                                                                     |        | 2,6                      | Standby power ( $P_{\text{sb}}$ ), expressed in W and rounded to the second decimal                                                                        | 0,00                   |
| Networked standby power ( $P_{\text{net}}$ ) for CLS, expressed in W and rounded to the second decimal                                                |        | -                        | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set                                                         | 80                     |
| Outer dimensions without separate control gear, lighting control                                                                                      | Height | 54                       | Spectral power distribution in the range 250 nm to 800 nm, at full-load                                                                                    | See image in last page |
|                                                                                                                                                       | Width  | 50                       |                                                                                                                                                            |                        |
|                                                                                                                                                       | Depth  | 50                       |                                                                                                                                                            |                        |

|                                                                                                                         |      |                                                                    |                |  |
|-------------------------------------------------------------------------------------------------------------------------|------|--------------------------------------------------------------------|----------------|--|
| parts and non-lighting control parts, if any (millimetre)                                                               |      |                                                                    |                |  |
| Claim of equivalent power <sup>(a)</sup>                                                                                | -    | If yes, equivalent power (W)                                       | -              |  |
|                                                                                                                         |      | Chromaticity coordinates (x and y)                                 | 0,463<br>0,420 |  |
| <b>Parameters for directional light sources:</b>                                                                        |      |                                                                    |                |  |
| Peak luminous intensity (cd)                                                                                            | 400  | Beam angle in degrees, or the range of beam angles that can be set | 36             |  |
| <b>Parameters for LED and OLED light sources:</b>                                                                       |      |                                                                    |                |  |
| R9 colour rendering index value                                                                                         | 0    | Survival factor                                                    | 0,90           |  |
| the lumen maintenance factor                                                                                            | 0,93 |                                                                    |                |  |
| <b>Parameters for LED and OLED mains light sources:</b>                                                                 |      |                                                                    |                |  |
| displacement factor (cos $\phi_1$ )                                                                                     | 0,70 | Colour consistency in McAdam ellipses                              | 6              |  |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | -(b) | If yes then replacement claim (W)                                  | -              |  |
| Flicker metric (Pst LM)                                                                                                 | 1,0  | Stroboscopic effect metric (SVM)                                   | 0,4            |  |


(a) '-': not applicable;

(b) '-': not applicable;



**EPREL registration number:** 2717827

Model placed on the Union market from 01/06/2026.



<https://eprel.ec.europa.eu/qr/2717827>

**Supplier:** Bailey, Electric & Electronics B.V. (Importer)

**Website:** [www.bailey.nl](http://www.bailey.nl)

**Customer care service:**

**Name:** Yvo Hendriks

**Website:** [www.bailey.nl](http://www.bailey.nl)

**Email:** [purchase@bailey.nl](mailto:purchase@bailey.nl)

**Phone:** +31 162 522446

**Address:**

Everdenberg 21  
4902TT Oosterhout  
Netherlands