



Main

Range	TeSys
Product name	TeSys VARIO
Device short name	VBF
Device application	Preventive maintenance
Product or component type	Enclosed switch disconnecter
Performance level	High performance
Poles description	3P
Control type	Rotary handle
Type of operator	Long handle
Handle colour	Black
Handle front plate colour	Black
Rotary handle padlocking	1 to 3 padlocks 4...8 mm

Complementary

Marking	0 - 1
[Ue] rated operational voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ithe] conventional enclosed thermal current	100 A
[Ie] rated operational current	68.5 A (AC-23A) at 400 V
Rated operational power in W	37 kW at 400 V (AC-23) 30 kW at 400 V (AC-3)
Intermittent duty class	30
Making capacity (I rms)	1250 A at 400 V AC-21A 1250 A at 400 V AC-22A 1250 A at 400 V AC-23A
[Icm] rated short-circuit making capacity	2.8 kA at 400 V at Ipeak
[Icw] rated short-time withstand Rms current	1500 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 125 A aM 10 kA at 400 V - associated fuse 125 A gG
Breaking capacity	1000 A at 400 V (AC-21A) 1000 A at 400 V (AC-22A) 1000 A at 400 V (AC-23A)
Mechanical durability	30000 cycles
Electrical durability	30000 Cycles AC-21 30000 cycles DC-1...5
Environmental characteristic	Standard environment
Suitability for isolation	Yes
Connections - terminals	Screw clamp terminals 70 mm ² - flexible - with cable end Screw clamp terminals 95 mm ² - solid
Tightening torque	22.6 N.m - on screw clamp terminals
Fire resistance	960 °C conforming to IEC 60595-2-1
Handle front plate dimension	90 x 90 mm
Height	280 mm
Width	220 mm
Depth	191 mm
Net weight	2.19 kg

Environment

Standards	IEC 60947-4-1 IEC 60204
Protective treatment	TC
IP degree of protection	IP65 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------