




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Surface Mounting Adapter**

Primary Product Color: **Blue**

Primary Product Material: **Polycarbonate**

Operating Temperature (Max): **85 °C [185 °F]**

Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

Features

Product Type Features

Connector Hardware Accessory Type	Surface Mounting Adapter
Hardware Accessory Function	Mounting

Body Features

Primary Product Color	Blue
Primary Product Material	Polycarbonate

Dimensions

Product Width	15.24 mm[.6 in]
Product Length	43.18 mm[1.699 in]
Product Height	5.1 mm[.2 in]

Usage Conditions

Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features



Packaging Method	Bag
Packaging Quantity	250

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

SURF MT ADAPTER,POWER LK,SRS2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_53885-1_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_53885-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_53885-1_P.3d_stp.zip

English

Customer View Model

ENG_CVM_53885-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_53885-1_E.3d_stp.zip

English

Customer View Model

ENG_CVM_53885-1_E.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

Japanese

Power-Lock 75 Series Contacts



Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English

Power Lock Connectors (Series II) (Accept Contacts 53880 and 54330)

English