








Código RS 517-3945  
 Código RS 517-3951  
 Código RS 517-3967  
 Código RS 517-3973  
 Código RS 517-3989  
 Código RS 517-3995  
 Código RS 517-4005  
 Código RS 517-4011

## Cajas de alta temperatura pintadas en negro (sin junta, pintadas en negro)



Código RS	Tamaño n.º	L	W	H	C1	C2	S1	S2	Espesor de la pared
5173945	A	89,4	35,3	30,6	79,3	25,3			1,5 mm
5173951	B	114,8	63,9	30,6	104,5	54,2			1,5 mm
5173967	D	114,7	64,4	55,4	104,6	54,2			2 mm
5173973	E	172,3	120,2	55,3	160,4	109,3			2 mm
5173989	J	275,3	175,3	65,8	264,1	164,0	132,2		2 mm
5173995	L	166,1	127,6	76,6	154,0	116,1	77,1		2 mm
5174005	M	120,2	100,3	36,0	108,5	88,4	50,1		2 mm
5174011	N	250,5	250,5	100,8	238,0	238,0	79,9	160,0	2,5 mm

- Material de la base y tapa: aleación de aluminio ADC12
- Material de los tornillos: acero inoxidable M3.5 × 9 mm, cabeza avellanada Supadrive
- Acabado: pintura
  - Grosor: 1,5 µm~2,0 µm (60~80 micropulgadas)
  - Color: Pantone 4C 2X (negro RAL 9005)
- Inclinación de 1,5° por tapa lateral hacia la base