


Features

- Ceramic Tube Fuses
- 5x20mm size
- RoHS compliant & Pb free

RS PRO - 5x20 mm, 250mA, 1500 mv HIGH-BREAKING CAPACITY CERAMIC TUBE FUSE (TIME-LAG)

RS Stock No.: 0666154



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Ceramic Fuse (High Breaking Capacity) - Time-Lag

Rated current: 250mA

Rated voltage: 1500 mv

Reference standards: IEC60127, GB9364

Application:

Electronics, electrical products, circuit protection. For example televisions, computers, washing machines, air conditioners and so on.

Electrical Specifications

Current Rating	20A
Operating Temperature	-55℃~125℃
Storage Temperature:	-55℃~85℃
Solderability:	245℃±5℃, 5s±0.5s
Fuse Type	Time-Lag Glass Fuse
Dimension	5x20 mm
Testing Standard	IEC 60127, GB 9364


Electrical Characteristics

RATING		BLOWING TIME			
		200mA - 800mA	1A-3.15A	4A-10A	>10A
2.1In	Max.	30 minutes	30 minutes	30 minutes	30 minutes
	Min.	250 ms	750 ms	750 ms	1 second
2.75In	Max.	80 seconds	80 seconds	80 seconds	80 seconds
	Min.	50 ms	95 ms	150 ms	150 ms
4In	Max.	5 seconds	5 seconds	5 seconds	5 seconds
	Min.	5 ms	10 ms	10 ms	20 ms
10In	Max.	150 ms	150 ms	150 ms	150 ms
	Min.	5 ms	10 ms	10 ms	20 ms

Approvals

Compliance/Certifications	UL
Declarations	IEC 60127, GB 9364

50CT



50CT AVERAGE I-T CHARACTERISTICS CURVE (FOR REFERENCE ONLY)

