Powerful performance, speed and durability

Kingston's Canvas Select Plus microSD is compatible with Android devices and designed with A1-rated performance. It offers improved speed and capacity for loading apps faster and capturing images and videos in multiple capacities up to 512 GB¹. Powerful in performance, speed and durability, the Canvas Select Plus microSD is designed for reliability when shooting and developing high-resolution photos or filming and editing full HD videos. Kingston Canvas cards are tested to be durable in the harshest environments and conditions so you can take them anywhere with confidence that your photos, videos and files will be protected. Available with a lifetime warranty.

- \rangle Class 10 UHS-I speeds up to 100 MB/s²
- > Optimised for use with Android devices
- > Capacities up to 512 GB¹
- > Durable
- > Lifetime Warranty



Features/specs on reverse $\rangle\rangle$



kingston.com/flash

FEATURES/BENEFITS

- > Faster speeds Class 10 UHS-I speeds up to 100 MB/s.²
- > Optimised for use with Android devices Improved performance when used with an Android smartphone or tablet.
- > Multiple capacities Up to 512 GB1 to store all your memorable photos and videos.
- > **Durable** For your peace of mind, the card has been extensively tested and proven to be waterproof, temperature proof, shock and vibration proof and X-ray proof.³

SPECIFICATIONS

- > Capacities¹ 16 GB, 32 GB, 64 GB, 128 GB, 256 GB, 512 GB
- > Performance² 100 MB/s read (16 GB-128 GB) 100/85 MB/s read/write (256 GB-512 GB)
- > **Dimensions** 11 mm x 15 mm x 1 mm (microSD) 24 mm x 32 mm x 2.1 mm (with SD adapter)
- > Format FAT32 (16 GB-32 GB), exFAT (64 GB-512 GB)
- > Operating temperature -25 °C~85 °C
- > Storage temperature -40 °C~85 °C
- >Voltage 3.3 V
- > Warranty/support lifetime



PART NUMBERS

Card (SD adapter included):

- SDCS2/16GB
- SDCS2/32GB
- SDCS2/64GB
- SDCS2/128GB
- SDCS2/256GB
- SDCS2/512GB

Multi-packs of 2 and 3 cards (1 SD adapter included):

- SDCS2/16GB-2P1A
- SDCS2/16GB-3P1A
- SDCS2/32GB-2P1A
- SDCS2/32GB-3P1A
- SDCS2/64GB-2P1A
- SDCS2/64GB-3P1A

- 1. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is les than what is listed on the products. For more information, go to Kingston's Flash Memory Guide at kingston.com/flashquide.
- 2. Speed may vary due to host and device configuration.
- 3. IEC/EN 60529 IPX7 certified for protection against continual water submersion up to 30 minutes at a depth of up to 1 m. Withstands temperature range from -25 °C to 85 °C. Based on MIL-STD-883H, METHOD 2002.5 military standard test method. Protected against X-ray exposure based on ISO7816-1 guidelines.



THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE. ©2019 Kingston Technology Europe Co LLP and Kingston Digital Europe Co LLP, Kingston Court, Brooklands Close, Sunbury-on-Thames, Middlesex, TW16 7EP, England. Tel: +44 (0) 1932 738888 Fax: +44 (0) 1932 785469 All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKK MKD-407EN



Card (SD adapter not included):

- SDCS2/16GBSP
- SDCS2/32GBSP
- SDCS2/64GBSP
- SDCS2/128GBSP
- SDCS2/256GBSP
- SDCS2/512GBSP