



Datasheet

RS Magnetic Base & Dial Indicator Kit


RS Stock number **841-2574**

	<p>Kit Contents:</p> <ul style="list-style-type: none"> 1 x Magnetic Base with Fine Adjustment 1 x Plunger Dial Indicator 10mm Travel / 0.01mm reading
---	--


Magnetic Base

	<p>Magnetic Base with Fine Adjustment Cross Arm Holds Plunger and Lever Indicators Plunger Indicators held on Lug Back or 8mm Stem Lever Indicators held on spigots Overall Height: 230mm Main Upright Post: 12mm dia. with M8 x 1.25 thread Fine Adjustment Cross Arm: 10mm dia. x 150mm long</p> <p>Magnetic Base with ON/OFF switch Magnetic Pull: 40kg (400N) Magnet Size: H=55mm W=50mm D=60mm</p>
---	---

Dial Indicator

	<p>General Specifications:</p> <ul style="list-style-type: none"> Adjustable dial Hardened & ground racks Bezel lock Lug back fitting Fitted with ball anvil Anvil thread 2.5mm
---	---

Code	Dial Dia./ mm	Travel / mm	Grads. / mm	Reading	Dial Colour
8412561	60	25.0	0.01	0-100 c/w, 0-100 a/c	White



Dimensions

Code	A	B	C	D	E	F	G	H	J	K	L	M
	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm
8412561	60	69.0	45.0	16.0	19.3	17.8	54.7	8.0	M2.5	8.0	20.0	18.0

Accuracy Specifications: Metric

Range	Grads.	Total Revs.	Each 0.1mm	Each 0.5mm	Each 1.0mm	Each 2mm	Total Travel
mm	mm		mm	mm	mm	mm	mm
0-10	0.01	10	0.005	0.008	0.01	0.015	0.020