

C55PB-PRO/8

Workstation for workshop equipment combination RSC55

Composed of:

C55B

Workbench with worktop (2050x700 mm) covered with a shockproof, nonscratch ABS coat resistant to oils and hydrocarbons.

Fitted with:

- Holes for a vice (1599F/150 - 1599GI/150, to be ordered separately)
- Vertically adjustable feet

C55C7

Mobile roller cab with seven drawers (588x367 mm) with ball bearing slides

- 4 castors Ø 100 mm, 2 fixed and 2 steering (one with brake)
- Aluminium opening system throughout length of drawer
- Drawer bases protected by foamed rubber mats
- Front centralized lock
- Can be fitted with thermoformed trays

C55MA

Fixed two-door module

- Push-pull opening system
- With lock
- Interior shelf, vertically adjustable

C55PS

Tool wall system with shutter and framework

- Aluminium shutter, vertically adjustable, with lock
- Removable perforated tool panel

 347 kg



	 art.	art.
	055000066	C55PB-PRO/8