

1590282

<https://www.phoenixcontact.com/gb/products/1590282>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, Axial O-ring, shielded: yes, number of positions: 26, connection method: Solder connection, series: HC

Commercial data

Item number	1590282
Packing unit	24 pc
Minimum order quantity	24 pc
Note	Made to order (non-returnable)
Sales key	ABRAJL
Product key	ABRAJL
GTIN	4046356186551
Weight per piece (including packing)	59.387 g
Weight per piece (excluding packing)	54.74 g
Customs tariff number	85366990
Country of origin	DE

HC-26P1N126300 - Device connector front mounting



1590282

<https://www.phoenixcontact.com/gb/products/1590282>

Technical data

Mounting

Mounting type	Front mounting Central fastening
Assembly note	Central fastening

Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 6.6
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	FPM

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Solder connection
Contact connection type	Pin

HC-26P1N126300 - Device connector front mounting



1590282

<https://www.phoenixcontact.com/gb/products/1590282>

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

HC-26P1N126300 - Device connector front mounting


1590282

<https://www.phoenixcontact.com/gb/products/1590282>




Drawings

Dimensional drawing



Housing bore holes

Dimensional drawing




Dimensional drawing

1590282

<https://www.phoenixcontact.com/gb/products/1590282>

Schematic diagram



Connector pin assignment

HC-26P1N126300 - Device connector front mounting



1590282

<https://www.phoenixcontact.com/gb/products/1590282>

Classifications

ECLASS

ECLASS-13.0	27440109
-------------	----------

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-26P1N126300 - Device connector front mounting



1590282

<https://www.phoenixcontact.com/gb/products/1590282>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	358409eb-6c65-4b4a-b5b1-90824f5ebbe2

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk