

Rittal – The System.

Faster – better – everywhere.

Compact system enclosures CM – CM 5116.500

Date : Nov 15, 2016

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Compact system enclosures CM – CM 5116.500

created: 15.11.2016 build on www.rittal.com/th-en



Product description

Material:	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Sheet steel 3.0 mm
Surface finish:	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55 with selection of the appropriate gland plates or trim panel
Protection category NEMA:	NEMA 12 with selection of the appropriate gland plates or trim panel
IK Code:	IK08
Supply includes:	Enclosure with hinged door(s) 3-point locking system with double-bit insert Mounting plate Open base for individual cable entry
Basic material:	Sheet steel

Product features

Dimensions:	Width: 800 mm Height: 1200 mm Depth: 300 mm
Mounting plate:	Width: 740 mm

Height: 1155 mm

Number of doors:	1
Door hinged on the right, may be swapped to the left:	yes
Packs of:	1 pc(s).
Weight/pack:	65 kg
EAN:	4028177479760
Customs tariff number:	94032080
ETIM 6.0:	EC000261
ETIM 5.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 7.0/7.1:	27180101
eCl@ss 6.0/6.1:	27180101
eCl@ss 5.1/5.1.4:	27180102

Approvals

Approvals:	CSA Lloyds Register of Shipping TÜV UL + C-UL
Certificates:	IK-Code
Declarations:	Declaration of conformity Manufacturer's declaration