




Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **82 Newton**
Product Length: **98 mm [3.9 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	82 Newton

Body Features

Primary Product Color	Natural
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	21 mm[.82 in]
Product Length	98 mm[3.9 in]
Product Width	2.49 mm[.098 in]
Product Thickness	1 mm[.039 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-160996-1
CABLE TY 200X3.6 NAT




TE Part # 4-160971-1
CABLE TY 140X3.6 NAT




TE Part # 171353-3
S-K BINDER CABLE TIE 3.2 INS




TE Part # 171353-2
CABLE TIES & BUNDLING 152.5 LG




TE Part # 2-160967-2
CABLE TY 98X2.5 BLA



TE Part # 2-160972-2
CABLE TY 290X3.6 BLA



TE Part # 2-160975-2
CABLE TY 200X4.8 BLA



TE Part # 2-160976-2
CABLE TY 250X4.8 BLACK

Customers Also Bought





TE Part #6-1393239-6
RT234024



TE Part #1601097-3
TAB,2.79X0.81,STD,SMZ



TE Part #1-640415-0
UMNL KEYING PLUG V0



TE Part #CAT-T3437-ST2999
STD Snap-On Markers



TE Part #D02886-000
B-155-9005



TE Part #1601046-2
WIRE2WIRE,STD,SMZ



TE Part #1-1971818-1
11P,RAST 2.5 Tab Header,Ex- Locking, THV



TE Part #2029047-3
3P MICRO MNL RCPT HSG SR SIDE



TE Part #5677862005
RNF-3000-9/3-9-STK

Documents

Product Drawings
CABLE TY 98X2.5 NAT

English

Datasheets & Catalog Pages
Connectivity Solutions for Industrial Applications

English

CABLE TIES
English