

PRODUCT DATASHEET

FL 50 P 41W 6KLM 865 PS SY100 BK

FLOODLIGHT 50 | Versatile floodlight with up to 6000 lm light output



PERFOR-
MANCE
CLASS

Areas of application

- Replacement for floodlights with halogen lamps
- Outdoor use (IP66)
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, e.g. by accumulation of dust
- Public areas
- Building facades
- Construction areas
- Parking
- Gardens and balconies

Product benefits

- Breather membrane to optimize air exchange, without compromising IP protection
- Highly versatile due to selectable lumen steps (Multi Lumen) on the housing
- Robust cable gland with integrated waterstop function
- Safe and very uniform illumination, due to frosted and tempered glass diffuser
- Bright, robust and durable
- Energy savings of up to 90 % compared to halogen lamp floodlights
- No upper light output ratio (ULOR 0%) when mounted at 0° tilt

Product features


- High luminous efficacy: up to 145 lm/W
- Type of protection: IP66
- Pre-installed, flexible 1 m cable (H05RN-F), wrapped 3 x 1.0 mm² single wires
- Reflector-based, symmetric light distribution with 100° x 100° beam angle
- Mounting bracket with 30° angle and wide rotation area

TECHNICAL DATA**Electrical data**


Nominal wattage	41 W / 27 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	185/130 mA
Inrush current	14.85 A
Inrush current time T_{h50}	33.6 μ s
Max. number of luminaires per miniature circuit breaker B16	50
Max. number of luminaires per miniature circuit breaker C10	40
Max. number of luminaires per miniature circuit breaker C16	64
Power factor λ	> 0.90
Total harmonic distortion	< 20 %
Protection class	I
Surge capability (L-N)	2 kV
Surge capability (L/N-Ground)	4 kV
Operating mode	Integrated LED driver

Photometrical data

Luminous flux	6000 lm / 4000 lm
Luminous efficacy	145 lm/W
Color temperature	6500 K
Light color (designation)	Cool Daylight
Color rendering index Ra	80
Standard deviation of color matching	5 sdc _m
Stroboscope effect metric (SVM)	≤0.9
Photobiological safety group acc. to EN62778	RG1
Photobiological safety group acc. to EN62471	RG1
Beam angle	100 ° x 100 °



FL 50 P 41W 6KLM 865 PS SY100 BK




FL 50 P 41W 6KLM 865 PS SY100 BK

Adjustable attributes

Nominal wattage	Color temperature	Luminous flux	Luminous efficacy
41 W	6500 K	6000 lm	145 lm/W
27 W	6500 K	4000 lm	145 lm/W

Dimensions & Weight

Length	201.00 mm
Width	43.00 mm
Height	179.00 mm
Product weight	830.00 g
Cable length	1000 mm



FL 50 P SY100

Materials & Colors

Product color	Black
Housing color	Black
RAL Color (most similar)	RAL 9017
Body material	Aluminum
Cover material	Glass
Light emitting surface material	Glass
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-30...+50 °C
Temperature range at storage	-40...+70 °C
Type of connection	Cable, 3-pole
Type of protection	IP66
Protection class IK (shock resistance)	IK07
Corrosion resistance class acc. to EN 12944	C4
Dimmable	No
Mounting type	Surface
Mounting location	Wall / Ceiling / Floor
Application environment	Outdoor
Mechanically adjustable	Yes
With light source	Yes
Replaceable light source	No

Lifespan

Lifespan L70/B50 at 25 °C	100000 h ¹⁾
Lifespan L80/B10 at 25 °C	75000 h ¹⁾
Lifespan L80/B50 at 25 °C	70000 h
Lifespan L90/B10 at 25 °C	35000 h

¹⁾ t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

Control gear

Output current	320 mA
ECG - Output ripple current	< 20 %

Certificates & Standards

Standards	CE / CB / ENEC / EAC / UKCA / EPD
-----------	-----------------------------------

Luminaire with limited surface temperature, "D sign"	Yes
Ball shot safe	No
EPD	LEDV-00031-V01.01-EN
Replaceable light source (EPREL)	Not replaceable

Additional product data

Added function	MULTI SELECT
----------------	--------------

Safety advice

– Max. wind load surface 0.025 m²

DOWNLOAD DATA

Documents and certificates		Document name
	User instruction / safety instructions	G11193706_UI_Floodlight_08W-41W
	Legal information	Insert_LSI_Floodlight_8_41w_G11195967
	Legal information	Informationstext 18 Abs 4 ElektroG
	Legal information	Safety Insert G11205496
	Legal information	Legal Insert G11277401
	Declarations of conformity	FLOODLIGHT GEN4
	Declarations of conformity UKCA	FLOODLIGHT GEN4
	EPD	EPD EN FLOODLIGHT GEN 4 LP SENSOR

Photometric and lighting design files		Document name
	IES file (IES)	FL 50 P 41W 6KLM 865 PS SY100 BK
	LDT file (Eulumdat)	FL 50 P 41W 6KLM 865 PS SY100 BK
	ULD file (DIALux)	FL 50 P 41W 6KLM 865 PS SY100 BK
	ROLF file (RELUX)	FL 50 P 41W 6KLM 865 PS SY100 BK

Photometric and lighting design files		Document name
	UGR file (UGR table)	FL 50 P 41W 6KLM 865 PS SY100 BK
	Light distribution curve type cone	FL 50 P 41W 6KLM 865 PS SY100 BK
	Light distribution curve type polar	FL 50 P 41W 6KLM 865 PS SY100 BK
CAD/BIM files		Document name
	BIM Revit 3D	Floodlight G4
	CAD STEP 3D	FL G4 41W
Tender texts		Document name
	Tender documents	FLOODLIGHT 50 41W 6KLM 865 PS SY100 BK-EN



LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854306006	Folding box 1	69 mm x 206 mm x 180 mm	911.00 g	2.56 dm ³
4099854306013	Shipping box 8	426 mm x 292 mm x 205 mm	7841.00 g	25.50 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

ADDITIONAL CATALOG INFORMATION

					230Vac		
A	B	C			C10A	B1A	C16A
8W	68	5.5	2x M4	0.012 m ²	78	88	125
17W	78	5.5	2x M4	0.014 m ²	81	102	131
41W	108	7.5	2x M6	0.025 m ²	40	50	64



		230Vac	
Product code	Power (W)	Power (W)	Power (W)
FL 10 P 40W 6KLM 865 PS SY100 BK	10	10	10
FL 15 P 40W 6KLM 865 PS SY100 BK	15	15	15
FL 20 P 40W 6KLM 865 PS SY100 BK	20	20	20
FL 25 P 40W 6KLM 865 PS SY100 BK	25	25	25
FL 30 P 40W 6KLM 865 PS SY100 BK	30	30	30
FL 35 P 40W 6KLM 865 PS SY100 BK	35	35	35
FL 40 P 40W 6KLM 865 PS SY100 BK	40	40	40
FL 45 P 40W 6KLM 865 PS SY100 BK	45	45	45
FL 50 P 40W 6KLM 865 PS SY100 BK	50	50	50
FL 55 P 40W 6KLM 865 PS SY100 BK	55	55	55
FL 60 P 40W 6KLM 865 PS SY100 BK	60	60	60
FL 65 P 40W 6KLM 865 PS SY100 BK	65	65	65
FL 70 P 40W 6KLM 865 PS SY100 BK	70	70	70
FL 75 P 40W 6KLM 865 PS SY100 BK	75	75	75
FL 80 P 40W 6KLM 865 PS SY100 BK	80	80	80
FL 85 P 40W 6KLM 865 PS SY100 BK	85	85	85
FL 90 P 40W 6KLM 865 PS SY100 BK	90	90	90
FL 95 P 40W 6KLM 865 PS SY100 BK	95	95	95
FL 100 P 40W 6KLM 865 PS SY100 BK	100	100	100

References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.