

Product data sheet

Specifications



Repacked, modular surge arrester with pluggable cartridge, Acti9, 1P+N, 350VAC, with remote transfer

A9L16282W



This repacked option saves 2.859 over the standard condition

Main

Range of product	IPRD1
range of product	Acti9
Product name	Acti9 iPRD1
Product or component type	Surge arrester with pluggable cartridge
Device short name	iPRD1 12.5
Device application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Quality labels	CE EAC VDE
Poles description	1P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TN-S TT

Complementary

Surge arrester class type	Type 1 + 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230 V AC (+/- 10 %) at 50/60 Hz
Nominal discharge current	20 kA
Maximum discharge current	50 kA
[Iimp] impulse current	Common mode: 50 kA N/PE Differential mode: 12.5 kA L/N
[Uc] maximum continuous operating voltage	Differential mode: 350 V L/N Common mode: 255 V N/PE
Maximum [Up] voltage protection level	<1.5 kV type 1 + 2
Residual current	0.003 mA N/PE
[Ut] temporary overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode
Disconnecter device type	Associated fuse gG 160 A 120 kA standard Associated circuit breaker Compact NSX160E 80 A 25 kA standard

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Local signalling	Operating: mechanical indicator (white) End of life: mechanical indicator (red)
Mounting mode	Clip-on (DIN rail)
9 mm pitches	4
Height	89 mm
Width	36 mm
Depth	69 mm
Product weight	290 g
Colour	White (RAL 9003)
Material	PA6
Connections - terminals	Tunnel type terminal (phase) 10...25 mm² flexible Tunnel type terminal (phase) 10...35 mm² rigid Tunnel type terminal (earth) 16...25 mm² flexible Tunnel type terminal (earth) 16...35 mm² rigid
Wire stripping length	14 mm
Tightening torque	3.5 N.m
Impulse current	12.5 kA
Compatibility code	IPRD1
Market segment	Residential Small commercial

Environment

IK degree of protection	IK05 conforming to IEC 62262
Pollution degree	3
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C
Circular nature	Repacked

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	8 cm
Package 1 Length	9 cm
Package 1 Weight	326 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	8.5 cm
Package 2 Width	10 cm
Package 2 Length	27.5 cm
Package 2 Weight	2.032 kg

Unit Type of Package 3	S02
Number of Units in Package 3	18
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.346 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

3 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A9614fa2-07f8-47d1-a2fe-e27b32003d8d

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins