



F 150 x 20 x 34 - 1 pc

CIRCULAR SAW BLADES FOR METAL

- 1. Engineered tooth geometry for optimum performance.
- 2. Top grade carbide and cermet tooth tips for superior lifetime.
- 3. Fully hardened and tensioned blade body for accurate cuts.
- 4. Deep gullets provide rapid and efficient chip removal.
- 5. Laser cut resin filled expansion slots for noise and vibration dampening.
- Cuts clean. Burr free edges reduce extra finishing processes.
- Cuts cool. The cut material can be handled immediately after cutting.
- Cuts fast. Quicker than all other conventional cutting methods.
- Cost cutter. Less expensive per cut than abrasive discs.
- Reduced noise.
- Reduced vibration.
- Total safety: no sparks, no coolants, cool to touch.
- Blade 4932478815 is supplied in natural silver finish



Aluminium	✓
Angle iron	✓
Article Number	48404080
Blade diameter (mm)	150
Bore size (mm)	20
Cutting width (kerf) (mm)	1.6
Material thickness (mm)	1-2.5
Materials suited for	Medium metal 1.5 - 4 mm Thin metal 0.5 - 3 mm Non ferrous metal (Cu/Al) Corrugated steel sheets up to 2.5mm sheet steel up to 2.5mm Mild Steel
Mild steel	✓