



Screw Extractors, Carbon Steel

Surface Treatment	Bright
Flute Geometry	Left Hand Spiral Flutes
Application	For extracting broken screws or studs by inserting the Extractor into a pre-drilled hole and turning anti-clockwise
Note:	A = on low or medium tensile screws B = on high tensile screws + 75 tons/sq inch. S = Screw size to be extracted.

Entry Code	No.	S	S	"A"	"A"	"B"	"B"	Entry Code	No.	S	S	"A"	"A"	"B"	"B"
		mm	inch /"	mm	inch /"	mm	mm			mm	inch /"	mm	inch /"	mm	mm
M1001	1	3 - 5	1/8 3/16	2,0	5/64	2,0	5/64	M1005	5	14	1/2 9/16	7,2	9/32	8,0	5/16
M1002	2	6	1/4	2,8	7/64	3,0	1/8	M1006	6	16 - 20	5/8 3/4	10,5	13/32	11,0	7/16
M1003	3	8 - 10	5/16 3/8	4,0	5/32	4,3	11/64	M1007	7	22 - 30	7/8 1.	13,5	17/32	14,5	9/16
M1004	4	12	7/16	5,5	7/32	6,0	15/64	M1008	8	33 - 42	1.3/8	20,5	13/16	21,5	27/32
								M1009	9	45	1.3/4	27,0	1.1/16	28,0	1.3/32