

DC Axial Fan

Features

- Electronically commutated DC motor
- With polarity reversal and blocking protection
- High output, quiet running
- Connecting wires 300 mm AWG 24
- Speed control
- Signal output



Specification

Rated Voltage	24 VDC
Operating Voltage	14 ... 26.4 V
Rated Speed	7000 rpm
Rated Current	1.1 A
Rated Power	26.4 W
Max. Airflow	145.57 CFM, 247.3 m ³ /h
Max. Air Pressure	1.46 inch-H ₂ O, 37.06 mm-H ₂ O
Noise	64.1 dBA, 68.1 dBA max.
Wire	2 Leads - 300 mm
Service Life	70000 hours @ 40 °C
Dielectric Strength	5 mA max @ 500 VAC 60 Hz 1 min.
Insulation Resistance	10 MOhm min. @ 500 VDC

Mechanical


Fan Size (See Dimension Drawing in Page 2)	92 x 92 x 38 mm
Frame	Thermoplastic Black / PBT 15% gf of UL94-V0
Fan Blade	Thermoplastic Black / PBT 15% gf of UL94-V0
Bearing	Ball Bearing
Weight	216 g

Environment


Ambient Operating Temperature	-10 ... 70 °C
Storage Temperature	-40 ... 75 °C
Operation Humidity	5 ... 90 % RH
Storage Humidity	5 ... 95 % RH

DC Axial Fan

Drawing



P-Q Curve



Art Nr.

RND 460-00067