

LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K

0051018

Range Features

- LED T5 batten 800lm/m ideal for cove lighting and secondary illumination
- LED T5 batten 1500lm/m high lumen output ideal for direct lighting such as under cabinet or in kitchens
- LED T5 batten 1500lm includes integrated switch
- Driver integrated, direct input 220-240V
- Seamless linking - up to 10m
- Tilttable mounting bracket included
- High quality robust PC extrusion tube
- Uniform light distribution
- Easy installation by mounting brackets (2 non-tiltable + 2 tilttable included)
- Available in approximately 300/600/900/1200mm length
- Available in 3000K and 4000K
- Low maintenance with 30,000 hours LED life expectancy
- LED technology provides energy efficient solution and reduced maintenance cost

PRODUCT OVERVIEW

Certifications	CE
Colour temperature (K)	3000
Colour	White
CRI (Ra)	80
EAN code	5410288510187
Luminous flux (lm)	2000
Housing	Polycarbonate
IP rating	IP20
Light colour	Warm white
LOR (%)	100
Mount	Surface mounted
Ordering number	0051018
Efficacy (Rated) (lm/w)	91
Average life (Rated) (h)	30000
Technology	LED
Voltage (V)	100-240
Included lamp	Integrated LED

DATA TABLE

General data

Certifications	CE
EAN code	5410288510187
Environment	Internal

LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K

0051018

General application	Residential & Consumer
Housing	Polycarbonate
Mount	Surface mounted
Ordering number	0051018
	LED T5 batten 800lm/m ideal for cove lighting and secondary illumination
	LED T5 batten 1500lm/m high lumen output ideal for direct lighting such as under cabinet or in kitchens
	LED T5 batten 1500lm includes integrated switch
	Driver integrated, direct input 220-240V
	Seamless linking - up to 10m
	Tiltable mounting bracket included
Range features	High quality robust PC extrusion tube
	Uniform light distribution
	Easy installation by mounting brackets (2 non-tiltable + 2 tiltable included)
	Available in approximately 300/600/900/1200mm length
	Available in 3000K and 4000K
	Low maintenance with 30,000 hours LED life expectancy
	LED technology provides energy efficient solution and reduced maintenance cost
Product name	LED PIPE 1500 2000LM 22W L1200 3000K
Average life (Rated) (h)	30000
Technology	LED
Product features	LED Batten T5 1500lm per metre, 2000LM, 22W, L1200, 3000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 1182mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.

Optical data

Colour temperature (K)	3000
CRI (Ra)	80
Distribution type	Direct
Luminous flux (lm)	2000
Light colour	Warm white
LOR (%)	100

Physical data

Colour	White
Diffuser finish	Frosted
Height (mm)	36
IP rating	IP20
Lamp included	Integrated
Length (mm)	1182
Width (mm)	24
Included lamp	Integrated LED

LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K

0051018


Electrical data

Electrical protection	CLASS 2
Efficacy (Rated) (lm/w)	91
Total power consumption (W)	22
Voltage (V)	100-240


PHOTOMETRY

Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)
0.5	10.78 1.43	1739 1	84.7° 55.1°	163
1.0	21.56 2.87	438 0	84.7° 55.1°	41
1.5	32.34 4.30	193 0	84.7° 55.1°	18
2.0	43.12 5.73	109 0	84.7° 55.1°	10
2.5	53.90 7.17	70 0	84.7° 55.1°	7
3.0	64.68 8.60	46 0	84.7° 55.1°	5


Distance [m] Cone diameter [m] Illuminance [lx]
 — C0 - C180 (Half beam angle: 110.2°)
 — C90 - C270 (Half beam angle: 166.4°)



TECHNICAL DRAWINGS



Typ	L1	L2	W	H
4/6W	270mm	262mm	24mm	36mm
7/11W	570mm	562mm	24mm	36mm
10/17W	670mm	662mm	24mm	36mm
14/22W	1170mm	1162mm	24mm	36mm



LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K

0051018

