

FEATURES

- Make use of both ends of the hex key
- The hex keys are heat treated to HRC 48~52
- A stylish, wear-resistant, vinyl storage, tool role ensures that the keys are kept from damage or getting lost
- Chemically blackened finish on each individual hex key

RS PRO 25 pieces Hex Key Set, L Shape 1.5mm

RS Stock No.: 537-827



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, this high-quality hex key set is a handy way to keep differing allen key sizes all in one place. With both long and short arm keys, in metric and imperial sizes, the set prepares you for a variety of hex driving eventualities. Supplied in a handy plastic holder, the keys are portable, neatly organized and ready for any task. The long arm L-wrenches are ideal for deep-set bolts.

What size are the keys?

The contents of this hex key set include:

- 12 pack - Imperial long series hex key wrenches - 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16" & 3/8"
- 13 pack - Metric short series hex key wrenches - 1.5, 2.0, 2.5, 3.0, 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0 and 10.0 mm

General Specifications

Imperial or Metric	Metric
Number of Pieces	25
Shape	L
Hex Key Type	Hexagon
Material	Chrome Vanadium Steel
Finish	Blackened
Height Safe	No
Set Contents	25pc. Metric hexagon L shape Long arm hex key
Applications	They are ideal for when fasteners need to be adjusted or equipment needs to be dismantled. From furniture assembly to bicycle maintenance

Electrical Specifications

Non-Sparking	No
---------------------	----

Mechanical Specifications

Short or Long Arm	Long
Hardness	Heat treated hex key to HRC 48 to 52

Dimensions

Hex Key Size	
Metric	Imperial
1.5mm	1/16in
2.0mm	5/64in
2.5mm	3/32in
3mm	5/64in
4mm	1/8in
4.5mm	9/64in
5mm	5/32in
5.5mm	3/16in
6mm	7/32in
7mm	1/4in
8mm	5/16in
9mm	3/8in
10mm	-

Approvals

VDE/1000V Approved	No
--------------------	----



