



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:44 (UTC)

MOTION & CONTROL
NSK



23136CE4

Spherical Roller Bearings

Boundary Dimensions


d	180	mm	Bore diameter
D	300	mm	Outside diameter
B	96	mm	Width
r (min.)	3	mm	Chamfer dimension

Basic Load Ratings

Cr	1320000	N	Basic dynamic load rating
C0r	1760000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	1700	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	2200	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	900	min-1	Grease lubrication
Oil (Oil-bath)	1200	min-1	Oil-bath lubrication



Abutment and Fillet Dimensions

da (min.)	194	mm	Diameter of shaft abutment
da (max.)	206	mm	Diameter of shaft abutment
Da (min.)	260	mm	Diameter of housing abutment
Da (max.)	286	mm	Diameter of housing abutment
ra (max.)	2.5	mm	Radius of shaft or housing fillet

Calculation factors

e	0.3	Constant
Y2	3.4	Axial load Factors
Y3	2.3	Axial load Factors
Y0	2.2	Axial load Factors

Mass

Mass approx.	27.5	kg	Mass approx.
--------------	------	----	--------------

