

Enamelled copper wire on mini bobbin  
**CUL 500/2,00**



## Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

## Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

## Approvals



## Enamelled copper wire on mini bobbin **CUL 500/2,00**

Type	CUL 500/2,00	Type	CUL 500/2,00	
Electrical data	<b>30</b>		<b>Operating data</b>	
			current car. cap.	11.50 A
			<b>Environment</b>	
			Heat resistance	155 °C (CL.F)
			insulating varnish	min. Polyurethan, mod.
			Tin-plate	>350 °C
			<b>Measures and weights</b>	
			Wire diameter	2.00 mm
			Weight	0.50 kg
			Length m (min.)	14

Subjects to change.