



Main

Range	Compact
Product name	Compact NSXm
Device short name	NSXm 80N
Product or component type	Circuit breaker
Device application	Distribution Protection

Complementary

[In] rated current	80 A
Poles description	4P 4d
Neutral position	Left
Control type	Toggle
Mounting mode	By screws for plate Clip-on for DIN rail
Network type	AC
Network frequency	50/60 Hz
Performance level	N
[Icu] rated ultimate breaking capacity	90 kA at 220...240 V AC 50/60 Hz according to IEC 60947-2 50 kA at 380...415 V AC 50/60 Hz according to IEC 60947-2 50 kA at 440 V AC 50/60 Hz according to IEC 60947-2
[Ue] rated operational voltage	690 V AC 50/60 Hz according to IEC 60947-2
[Ics] rated service breaking capacity	90 kA at 220...240 V AC 50/60 Hz according to IEC 60947-2 50 kA at 380...415 V AC 50/60 Hz according to IEC 60947-2 50 kA at 440 V AC 50/60 Hz according to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV according to IEC 60947-2
[Ui] rated insulation voltage	800 V according to IEC 60947-2
Trip unit technology	Thermal-magnetic
Trip unit name	TM-D
Trip unit protection functions	LI

Trip unit rating	80 A at 40 °C
Protection type	Short-circuit protection (magnetic) Overload protection (thermal)
Long time pick-up adjustment range	0.7...1 x In
Short-time pick-up adjustment type lsd	Fixed
Short-time delay adjustment type	Fixed
Magnetic hold current	800 A
Magnetic tripping current	1200 A
Suitability for isolation	Yes according to IEC 60947-2
Utilisation category	Category A
9 mm pitches	12 module
Connection pitch	35 mm with spreaders 27 mm without spreaders
Connections - terminals	1 Everlink lug 2.5...70 mm ² (flexible) conductor :copper 1 Everlink lug 2.5...95 mm ² (rigid or stranded) conductor :aluminium/copper
Tightening torque	5 N.m for 2.5...10 mm ² 9 N.m for 16...95 mm ²
Local signalling	Green flag for presence of auxiliary contacts
Number of slots	1 slot(s) for auxiliary switch OF 1 slot(s) for alarm switch SD 1 slot(s) for voltage release MN or MX
Power wire stripping length	20 mm

Environment

Quality labels	CE
Standards	EN/IEC 60947
Product certifications	CCC EAC Marine
Colour	Grey (RAL 7016)
IP degree of protection	IP40 (front cover) according to IEC 60529
IK degree of protection	IK07 according to IEC 62262
Pollution degree	3 according to IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	5000 m with derating 2000 m without derating
Mechanical durability	20000 cycles according to IEC 947-1 Annex K ed 5.2 for In
Electrical durability	10000 cycles according to IEC 947-1 Annex F ed 5.2 for In at 440 V
Height	137 mm
Width	108 mm
Depth	80 mm
Product weight	1.42 kg
Quantity per set	Set of 1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1649 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Need no specific recycling operations