



PartNumber	192900-0286
Product Family	Trident
Product Group	Neptune, Accessory, TNM
Used Connector	Neptune
Environmental Sealing	Up to IP65
Flammability	UL 94V-0
Component	Accessory
Footnote	Dimensions are in mm (inch). Dimensions are subject to change.
For more information	Contact Cannon Sales Department
Type of Accessory	Cable Clamp
Packaging	Single
Type of Cable Clamps	Unsealed
Shell Size	14
Note 1	Dimension E, for disassembly: For Neptune Shell Sizes 14 & 16 and TNM Shell Sizes 10-16 add 9,00 (.354). For Neptune Shell Size 24 add 10,60 (.417).
Dimension A	Ø27,00 (1.063) max.
Dimension B	6,40 ±0,20 (.251 ±.007)
Dimension C	Ø13,80 (.543) max.
Dimension D	Ø27,00 ±0,15 (1.063 ±.005)
Dimension E	Neptune Only: 67,10 (2.641) max.
Dimension E (Standard)	TNM Only: 80,50 (3.169) max.

Dimension E (Reversed)

TNM Only: 71,80 (2.826) max.

Nomenclature

TNA14CCSR-00L

